

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P582295

Luminaire Tested: **HCC6W35D010MW-HM63040830-61PSMDW**

Issue Date: 9/16/2021

Test Information

Test Method: LM-41-14
Report Number: P582295
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2105-241-12)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/16/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC6W35D010MW-HM63040830-61PSMDW
Description: HALO COMMERCIAL 6" ROUND, NEW CONSTRUCTION FRAME, WITH 6" PLASTIC TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 3000K CCT
CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3695.0 lumens
Efficiency: N/A
Efficacy: 109.6 lumens/watt
Spacing Criteria (0/90/45): 1.09 / 1.09 / 1.04
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 33.7
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P582295
CATALOG NUMBER: HCC6W35D010MW-HM63040830-61PSMDW

Luminous Intensity Polar Plot





TEST NUMBER: P582295

CATALOG NUMBER: HCC6W35D010MW-HM63040830-61PSMDW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	111	107	104	101	108	105	102	99	101	98	96	97	95	93	93	92	90	88			
2	103	96	91	86	101	95	90	85	91	87	83	88	85	82	85	82	80	78			
3	96	87	81	75	94	86	80	75	83	78	73	80	76	72	78	74	71	69			
4	89	80	72	67	87	78	72	66	76	70	65	74	69	65	72	67	64	62			
5	84	73	65	60	82	72	65	59	70	64	59	68	63	58	66	62	58	56			
6	78	67	59	54	77	66	59	54	64	58	53	63	57	53	61	56	53	51			
7	73	62	54	49	72	61	54	49	60	53	49	58	53	48	57	52	48	46			
8	69	57	50	45	68	57	50	45	56	49	45	54	49	44	53	48	44	43			
9	65	53	46	41	64	53	46	41	52	46	41	51	45	41	50	45	41	39			
10	62	50	43	38	60	49	43	38	49	42	38	48	42	38	47	42	38	36			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	132062
5°	131708
10°	129740
15°	127691
20°	123485
25°	117618
30°	107396
35°	86465
40°	58273
45°	42493
50°	36724
55°	33184
60°	31478
65°	29796
70°	28018
75°	26540
80°	24719
85°	22958



TEST NUMBER: P582295

CATALOG NUMBER: HCC6W35D010MW-HM63040830-61PSMDW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	226.5	6.1
10°-20°	631.8	17.1
20°-30°	887.7	24.0
30°-40°	790.2	21.4
40°-50°	441.6	12.0
50°-60°	314.6	8.5
60°-70°	228.9	6.2
70°-80°	132.5	3.6
80°-90°	41.2	1.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1746.0	47.3
0°-40°	2536.2	68.6
0°-60°	3292.4	89.1
0°-90°	3695.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3695.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2409	
5°	2393	227
15°	2250	632
25°	1944	888
35°	1292	790
45°	548	442
55°	347	315
65°	230	229
75°	125	133
85°	36	41
90°	0	



TEST NUMBER: P582295

CATALOG NUMBER: HCC6W35D010MW-HM63040830-61PSMDW

CANDELA DISTRIBUTION (FULL):

0°	
0°	2409.0
2.5°	2398.7
5°	2393.4
7.5°	2372.5
10°	2330.7
12.5°	2291.6
15°	2249.9
17.5°	2192.4
20°	2116.7
22.5°	2033.3
25°	1944.5
27.5°	1834.9
30°	1696.6
32.5°	1519.1
35°	1292.0
37.5°	1036.2
40°	814.3
42.5°	649.9
45°	548.1
47.5°	480.2
50°	430.6
52.5°	386.3
55°	347.2
57.5°	315.8
60°	287.1
62.5°	261.1
65°	229.7
67.5°	203.6
70°	174.8
72.5°	148.8
75°	125.3
77.5°	101.8
80°	78.3
82.5°	57.4
85°	36.5
87.5°	18.3
90°	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)