

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P582291

Luminaire Tested: **HCC6W35D010SL-HM63040830-61MDW**

Issue Date: 9/16/2021

Test Information

Test Method: LM-41-14
Report Number: P582291
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2105-241-6)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/16/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC6W35D010SL-HM63040830-61MDW
Description: HALO COMMERCIAL 6" ROUND, NEW CONSTRUCTION FRAME, WITH 6" MEDIUM DISTRIBUTION, WHITE TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 3000K CCT
CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3603.6 lumens
Efficiency: N/A
Efficacy: 106.9 lumens/watt
Spacing Criteria (0/90/45): 1.08 / 1.08 / 1.03
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 33.7
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P582291
CATALOG NUMBER: HCC6W35D010SL-HM63040830-61MDW

Luminous Intensity Polar Plot





TEST NUMBER: P582291
 CATALOG NUMBER: HCC6W35D010SL-HM63040830-61MDW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10		0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	111	108	104	101	109	105	102	100	101	99	96	97	95	94	94	92	91	89		
2	104	97	92	87	101	95	90	86	92	88	84	89	85	82	86	83	81	79		
3	97	88	82	76	94	87	81	76	84	79	75	81	77	73	79	75	72	70		
4	90	80	73	68	88	79	73	67	77	71	67	75	70	66	73	68	65	63		
5	84	74	66	61	82	73	66	61	71	65	60	69	64	59	67	63	59	57		
6	79	68	61	55	77	67	60	55	65	59	55	64	58	54	62	58	54	52		
7	74	63	55	50	73	62	55	50	61	54	50	59	54	50	58	53	49	48		
8	70	58	51	46	69	58	51	46	57	50	46	55	50	46	54	49	45	44		
9	66	54	47	43	65	54	47	42	53	47	42	52	46	42	51	46	42	40		
10	62	51	44	39	61	50	44	39	49	43	39	49	43	39	48	43	39	37		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	134150
5°	133656
10°	131427
15°	129104
20°	124652
25°	118192
30°	107504
35°	85902
40°	57315
45°	40857
50°	34037
55°	29667
60°	28035
65°	26397
70°	24267
75°	22664
80°	20583
85°	18052



TEST NUMBER: P582291
 CATALOG NUMBER: HCC6W35D010SL-HM63040830-61MDW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	229.7	6.4
10°-20°	638.7	17.7
20°-30°	892.6	24.8
30°-40°	786.3	21.8
40°-50°	424.8	11.8
50°-60°	284.0	7.9
60°-70°	201.3	5.6
70°-80°	113.2	3.1
80°-90°	33.0	0.9
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1761.0	48.9
0°-40°	2547.3	70.7
0°-60°	3256.1	90.4
0°-90°	3603.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3603.6	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2447	
5°	2429	230
15°	2275	639
25°	1954	893
35°	1284	786
45°	527	425
55°	310	284
65°	204	201
75°	107	113
85°	29	33
90°	0	



TEST NUMBER: P582291
CATALOG NUMBER: HCC6W35D010SL-HM63040830-61MDW

CANDELA DISTRIBUTION (FULL):

0°	
0°	2447.1
2.5°	2434.0
5°	2428.8
7.5°	2405.3
10°	2361.0
12.5°	2319.2
15°	2274.8
17.5°	2214.8
20°	2136.7
22.5°	2050.5
25°	1954.0
27.5°	1841.8
30°	1698.3
32.5°	1521.0
35°	1283.6
37.5°	1025.2
40°	800.9
42.5°	631.3
45°	527.0
47.5°	456.5
50°	399.1
52.5°	352.2
55°	310.4
57.5°	281.7
60°	255.7
62.5°	229.5
65°	203.5
67.5°	177.4
70°	151.4
72.5°	127.8
75°	107.0
77.5°	86.1
80°	65.2
82.5°	46.9
85°	28.7
87.5°	13.1
90°	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)