

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P582308

Luminaire Tested: **HCC6W35D010MW-HM63040835-61MDH**

Issue Date: 9/16/2021

Test Information

Test Method: LM-41-14
Report Number: P582308
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2105-241-5)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/16/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC6W35D010MW-HM63040835-61MDH
Description: HALO COMMERCIAL 6" ROUND, NEW CONSTRUCTION FRAME, WITH 6" MEDIUM DISTRIBUTION, HAZE TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 3500K CCT
CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3837.1 lumens
Efficiency: N/A
Efficacy: 113.9 lumens/watt
Spacing Criteria (0/90/45): 1.01 / 1.01 / 0.97
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 33.7
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P582308
CATALOG NUMBER: HCC6W35D010MW-HM63040835-61MDH

Luminous Intensity Polar Plot





TEST NUMBER: P582308
 CATALOG NUMBER: HCC6W35D010MW-HM63040835-61MDH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	113	110	108	105	111	108	106	104	104	102	100	100	99	97	97	96	94	93
2	107	102	98	94	105	100	96	93	97	94	91	94	91	89	91	89	87	85
3	101	94	89	85	99	93	88	84	90	86	83	88	84	81	86	83	80	79
4	96	88	82	77	94	86	81	77	84	79	76	82	78	75	80	77	74	72
5	90	81	75	71	89	80	75	70	79	74	70	77	73	69	75	72	68	67
6	85	76	70	65	84	75	69	65	74	68	64	72	67	64	71	67	63	62
7	81	71	65	60	79	70	64	60	69	64	60	68	63	59	67	62	59	57
8	77	67	60	56	75	66	60	56	65	59	55	64	59	55	63	58	55	53
9	73	62	56	52	72	62	56	52	61	56	52	60	55	52	59	55	51	50
10	69	59	53	49	68	58	52	48	57	52	48	57	52	48	56	51	48	47

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	192178
5°	192015
10°	190015
15°	186193
20°	176375
25°	159275
30°	135306
35°	99896
40°	57773
45°	30662
50°	17330
55°	9061
60°	5932
65°	4229
70°	3029
75°	2309
80°	1705
85°	1698



TEST NUMBER: P582308
 CATALOG NUMBER: HCC6W35D010MW-HM63040835-61MDH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	330.7	8.6
10°-20°	917.6	23.9
20°-30°	1197.6	31.2
30°-40°	915.2	23.9
40°-50°	331.3	8.6
50°-60°	96.2	2.5
60°-70°	34.4	0.9
70°-80°	11.8	0.3
80°-90°	2.2	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2445.9	63.7
0°-40°	3361.1	87.6
0°-60°	3788.7	98.7
0°-90°	3837.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3837.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3506	
5°	3489	331
15°	3281	918
25°	2633	1198
35°	1493	915
45°	396	331
55°	95	96
65°	33	34
75°	11	12
85°	3	2
90°	0	



TEST NUMBER: P582308

CATALOG NUMBER: HCC6W35D010MW-HM63040835-61MDH

CANDELA DISTRIBUTION (FULL):

	0°
0°	3505.6
2.5°	3489.3
5°	3489.3
7.5°	3464.9
10°	3413.5
12.5°	3353.8
15°	3280.7
17.5°	3172.4
20°	3023.3
22.5°	2839.2
25°	2633.2
27.5°	2400.3
30°	2137.5
32.5°	1842.2
35°	1492.7
37.5°	1127.0
40°	807.3
42.5°	558.1
45°	395.5
47.5°	284.4
50°	203.2
52.5°	143.5
55°	94.8
57.5°	67.7
60°	54.1
62.5°	43.3
65°	32.6
67.5°	27.1
70°	18.9
72.5°	13.5
75°	10.9
77.5°	8.2
80°	5.4
82.5°	2.7
85°	2.7
87.5°	0.0
90°	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)