

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P593235

Luminaire Tested: **HCC6S35D010MW-HM63040850-61NDH**

Issue Date: 9/16/2021

Test Information

Test Method: LM-41-14
Report Number: P593235
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2105-241-2)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/16/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC6S35D010MW-HM63040850-61NDH
Description: HALO COMMERCIAL 6" ROUND, NEW CONSTRUCTION FRAME, WITH 6" NARROW DISTRIBUTION, HAZE TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 5000K CCT
CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4131.2 lumens
Efficiency: N/A
Efficacy: 122.6 lumens/watt
Spacing Criteria (0/90/45): 0.89 / 0.89 / 0.89
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 33.7
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P593235
CATALOG NUMBER: HCC6S35D010MW-HM63040850-61NDH

Luminous Intensity Polar Plot





TEST NUMBER: P593235
 CATALOG NUMBER: HCC6S35D010MW-HM63040850-61NDH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	113	111	108	106	111	109	106	104	105	103	101		101	99	98		97	96	95	93
2	108	103	99	96	106	101	98	94	98	95	92		95	93	90		92	90	89	87
3	102	96	91	87	100	95	90	86	92	88	85		90	86	84		87	85	82	81
4	97	90	84	80	95	88	83	79	86	82	78		84	81	78		82	79	77	75
5	92	84	78	74	91	83	77	73	81	76	73		79	75	72		78	74	71	70
6	88	79	73	68	86	78	72	68	76	71	68		75	71	67		74	70	67	65
7	83	74	68	64	82	73	67	63	72	67	63		71	66	63		70	66	62	61
8	79	70	64	59	78	69	63	59	68	63	59		67	62	59		66	62	59	57
9	75	66	60	56	74	65	59	56	64	59	55		63	59	55		62	58	55	54
10	72	62	56	52	71	62	56	52	61	56	52		60	55	52		59	55	52	51

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	252902
5°	251832
10°	245871
15°	233395
20°	208029
25°	175238
30°	139616
35°	99608
40°	53565
45°	22948
50°	10439
55°	3804
60°	1864
65°	1479
70°	1362
75°	593
80°	884
85°	0



TEST NUMBER: P593235
 CATALOG NUMBER: HCC6S35D010MW-HM63040850-61NDH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	432.0	10.5
10°-20°	1139.9	27.6
20°-30°	1320.2	32.0
30°-40°	912.9	22.1
40°-50°	263.6	6.4
50°-60°	45.4	1.1
60°-70°	11.6	0.3
70°-80°	4.5	0.1
80°-90°	1.1	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2892.1	70.0
0°-40°	3805.0	92.1
0°-60°	4114.0	99.6
0°-90°	4131.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4131.2	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	4613	
5°	4576	432
15°	4112	1140
25°	2897	1320
35°	1488	913
45°	296	264
55°	40	45
65°	11	12
75°	3	4
85°	0	1
90°	0	



TEST NUMBER: P593235
CATALOG NUMBER: HCC6S35D010MW-HM63040850-61NDH

CANDELA DISTRIBUTION (FULL):

	0°
0°	4613.3
2.5°	4593.3
5°	4576.3
7.5°	4525.0
10°	4416.9
12.5°	4285.9
15°	4112.4
17.5°	3867.6
20°	3565.9
22.5°	3232.9
25°	2897.1
27.5°	2552.8
30°	2205.6
32.5°	1858.3
35°	1488.4
37.5°	1104.2
40°	748.5
42.5°	472.4
45°	296.0
47.5°	190.7
50°	122.4
52.5°	74.0
55°	39.8
57.5°	22.8
60°	17.0
62.5°	14.2
65°	11.4
67.5°	8.5
70°	8.5
72.5°	5.7
75°	2.8
77.5°	2.8
80°	2.8
82.5°	2.8
85°	0.0
87.5°	0.0
90°	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)