

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P593243

Luminaire Tested: **HCC6S35D010MB-HM63040850-61PSMDW**

Issue Date: 9/16/2021

Test Information

Test Method: LM-41-14
Report Number: P593243
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2105-241-12)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/16/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC6S35D010MB-HM63040850-61PSMDW
Description: HALO COMMERCIAL 6" ROUND, NEW CONSTRUCTION FRAME, WITH 6" PLASTIC TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 5000K CCT
CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4028.9 lumens
Efficiency: N/A
Efficacy: 119.6 lumens/watt
Spacing Criteria (0/90/45): 1.09 / 1.09 / 1.04
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 33.7
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P593243
CATALOG NUMBER: HCC6S35D010MB-HM63040850-61PSMDW

Luminous Intensity Polar Plot





TEST NUMBER: P593243
 CATALOG NUMBER: HCC6S35D010MB-HM63040850-61PSMDW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				
1	111	107	104	101	108	105	102	99	101	98	96	97	95	93	93	92	90	88				
2	103	96	91	86	101	95	90	85	91	87	83	88	85	82	85	82	80	78				
3	96	87	81	75	94	86	80	75	83	78	73	80	76	72	78	74	71	69				
4	89	80	72	67	87	78	72	66	76	70	65	74	69	65	72	67	64	62				
5	84	73	65	60	82	72	65	59	70	64	59	68	63	58	66	62	58	56				
6	78	67	59	54	77	66	59	54	64	58	53	63	57	53	61	56	53	51				
7	73	62	54	49	72	61	54	49	60	53	49	58	53	48	57	52	48	46				
8	69	57	50	45	68	57	50	45	56	49	45	54	49	44	53	48	44	43				
9	65	53	46	41	64	53	46	41	52	46	41	51	45	41	50	45	41	39				
10	62	50	43	38	60	49	43	38	49	42	38	48	42	38	47	42	38	36				

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	144002
5°	143616
10°	141469
15°	139229
20°	134651
25°	128245
30°	117094
35°	94275
40°	63548
45°	46330
50°	40050
55°	36176
60°	34328
65°	32481
70°	30566
75°	28954
80°	26961
85°	25034



TEST NUMBER: P593243
 CATALOG NUMBER: HCC6S35D010MB-HM63040850-61PSMDW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	247.0	6.1
10°-20°	688.9	17.1
20°-30°	967.9	24.0
30°-40°	861.6	21.4
40°-50°	481.5	12.0
50°-60°	343.1	8.5
60°-70°	249.6	6.2
70°-80°	144.5	3.6
80°-90°	44.9	1.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1903.8	47.3
0°-40°	2765.4	68.6
0°-60°	3589.9	89.1
0°-90°	4028.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4028.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2627	
5°	2610	247
15°	2453	689
25°	2120	968
35°	1409	862
45°	598	481
55°	378	343
65°	250	250
75°	137	145
85°	40	45
90°	0	



TEST NUMBER: P593243
CATALOG NUMBER: HCC6S35D010MB-HM63040850-61PSMDW

CANDELA DISTRIBUTION (FULL):

	0°
0°	2626.8
2.5°	2615.4
5°	2609.8
7.5°	2586.9
10°	2541.4
12.5°	2498.7
15°	2453.2
17.5°	2390.6
20°	2308.1
22.5°	2216.9
25°	2120.2
27.5°	2000.7
30°	1849.8
32.5°	1656.3
35°	1408.7
37.5°	1129.9
40°	888.0
42.5°	708.6
45°	597.6
47.5°	523.6
50°	469.6
52.5°	421.2
55°	378.5
57.5°	344.4
60°	313.1
62.5°	284.6
65°	250.4
67.5°	222.0
70°	190.7
72.5°	162.2
75°	136.7
77.5°	111.0
80°	85.4
82.5°	62.7
85°	39.8
87.5°	20.0
90°	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)