

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P582346

Luminaire Tested: **HCC6W35D010MW-HM63040927-61NDC**

Issue Date: 9/16/2021

Test Information

Test Method: LM-41-14
Report Number: P582346
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2105-241-1)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/16/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC6W35D010MW-HM63040927-61NDC
Description: HALO COMMERCIAL 6" ROUND, NEW CONSTRUCTION FRAME, WITH 6" NARROW DISTRIBUTION, SPECULAR TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3128.0 lumens
Efficiency: N/A
Efficacy: 92.8 lumens/watt
Spacing Criteria (0/90/45): 0.93 / 0.93 / 0.88
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 33.7
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P582346
CATALOG NUMBER: HCC6W35D010MW-HM63040927-61NDC

Luminous Intensity Polar Plot





TEST NUMBER: P582346
 CATALOG NUMBER: HCC6W35D010MW-HM63040927-61NDC

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	114	111	108	106	111	109	107	105	105	103	101		101	100	98		98	97	96	94
2	108	103	99	96	106	102	98	95	98	96	93		96	93	91		93	91	89	87
3	103	97	92	88	101	95	91	87	93	89	86		90	87	84		88	85	83	82
4	98	90	85	81	96	89	84	80	87	83	79		85	81	79		83	80	78	76
5	93	85	79	75	91	84	78	75	82	77	74		80	76	73		79	75	73	71
6	88	80	74	70	87	79	73	69	77	73	69		76	72	68		75	71	68	67
7	84	75	69	65	83	74	69	65	73	68	64		72	67	64		71	67	64	62
8	80	71	65	61	79	70	65	61	69	64	60		68	64	60		67	63	60	59
9	76	67	61	57	75	66	61	57	65	60	57		65	60	57		64	60	56	55
10	73	63	58	54	72	63	57	54	62	57	54		61	57	53		61	56	53	52

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	186800
5°	187172
10°	190255
15°	191641
20°	175179
25°	137657
30°	100762
35°	71474
40°	33806
45°	12901
50°	5782
55°	1577
60°	680
65°	532
70°	337
75°	445
80°	0
85°	0



TEST NUMBER: P582346
 CATALOG NUMBER: HCC6W35D010MW-HM63040927-61NDC

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	325.4	10.4
10°-20°	933.3	29.8
20°-30°	1038.1	33.2
30°-40°	648.5	20.7
40°-50°	154.1	4.9
50°-60°	22.1	0.7
60°-70°	4.6	0.1
70°-80°	1.9	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2296.8	73.4
0°-40°	2945.3	94.2
0°-60°	3121.4	99.8
0°-90°	3128.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3128.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3408	
5°	3401	325
15°	3377	933
25°	2276	1038
35°	1068	649
45°	166	154
55°	16	22
65°	4	5
75°	2	2
85°	0	0
90°	0	



TEST NUMBER: P582346
CATALOG NUMBER: HCC6W35D010MW-HM63040927-61NDC

CANDELA DISTRIBUTION (FULL):

0°	
0°	3407.5
2.5°	3393.1
5°	3401.3
7.5°	3413.6
10°	3417.8
12.5°	3415.7
15°	3376.7
17.5°	3245.2
20°	3002.8
22.5°	2661.9
25°	2275.8
27.5°	1906.1
30°	1591.8
32.5°	1331.0
35°	1068.0
37.5°	784.6
40°	472.4
42.5°	273.2
45°	166.4
47.5°	106.8
50°	67.8
52.5°	39.0
55°	16.5
57.5°	8.2
60°	6.2
62.5°	6.2
65°	4.1
67.5°	4.1
70°	2.1
72.5°	2.1
75°	2.1
77.5°	2.1
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)