

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P582345

Luminaire Tested: **HCC6S35D010MB-HM63040927-61MDW**

Issue Date: 9/16/2021

Test Information

Test Method: LM-41-14
Report Number: P582345
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2105-241-6)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/16/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC6S35D010MB-HM63040927-61MDW
Description: HALO COMMERCIAL 6" ROUND, NEW CONSTRUCTION FRAME, WITH 6" MEDIUM DISTRIBUTION, WHITE TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT
CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2836.2 lumens
Efficiency: N/A
Efficacy: 84.2 lumens/watt
Spacing Criteria (0/90/45): 1.08 / 1.08 / 1.03
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 33.7
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P582345
CATALOG NUMBER: HCC6S35D010MB-HM63040927-61MDW

Luminous Intensity Polar Plot





TEST NUMBER: P582345
 CATALOG NUMBER: HCC6S35D010MB-HM63040927-61MDW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	111	108	104	101	109	105	102	100	101	99	96	97	95	94	94	92	91	89
2	104	97	92	87	101	95	90	86	92	88	84	89	85	82	86	83	81	79
3	97	88	82	76	94	87	81	76	84	79	75	81	77	73	79	75	72	70
4	90	80	73	68	88	79	73	67	77	71	67	75	70	66	73	68	65	63
5	84	74	66	61	82	73	66	61	71	65	60	69	64	59	67	63	59	57
6	79	68	61	55	77	67	60	55	65	59	55	64	58	54	62	58	54	52
7	74	63	55	50	73	62	55	50	61	54	50	59	54	50	58	53	49	48
8	70	58	51	46	69	58	51	46	57	50	46	55	50	46	54	49	45	44
9	66	54	47	43	65	54	47	42	53	47	42	52	46	42	51	46	42	40
10	62	51	44	39	61	50	44	39	49	43	39	49	43	39	48	43	39	37

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	105578
5°	105189
10°	103438
15°	101612
20°	98102
25°	93024
30°	84614
35°	67606
40°	45106
45°	32158
50°	26797
55°	23359
60°	22060
65°	20767
70°	19074
75°	17813
80°	16195
85°	14215



TEST NUMBER: P582345
 CATALOG NUMBER: HCC6S35D010MB-HM63040927-61MDW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	180.8	6.4
10°-20°	502.7	17.7
20°-30°	702.5	24.8
30°-40°	618.8	21.8
40°-50°	334.3	11.8
50°-60°	223.6	7.9
60°-70°	158.4	5.6
70°-80°	89.0	3.1
80°-90°	26.0	0.9
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1386.0	48.9
0°-40°	2004.8	70.7
0°-60°	2562.7	90.4
0°-90°	2836.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2836.2	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1926	
5°	1912	181
15°	1790	503
25°	1538	702
35°	1010	619
45°	415	334
55°	244	224
65°	160	158
75°	84	89
85°	23	26
90°	0	



TEST NUMBER: P582345
CATALOG NUMBER: HCC6S35D010MB-HM63040927-61MDW

CANDELA DISTRIBUTION (FULL):

	0°
0°	1925.9
2.5°	1915.6
5°	1911.5
7.5°	1893.1
10°	1858.2
12.5°	1825.3
15°	1790.4
17.5°	1743.3
20°	1681.6
22.5°	1613.8
25°	1537.9
27.5°	1449.6
30°	1336.7
32.5°	1197.0
35°	1010.2
37.5°	807.0
40°	630.3
42.5°	496.9
45°	414.8
47.5°	359.3
50°	314.2
52.5°	277.2
55°	244.4
57.5°	221.7
60°	201.2
62.5°	180.7
65°	160.1
67.5°	139.6
70°	119.0
72.5°	100.6
75°	84.1
77.5°	67.8
80°	51.3
82.5°	37.0
85°	22.6
87.5°	10.3
90°	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)