

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P582348

Luminaire Tested: **HCC6W35D010SL-HM63040927-61NDW**

Issue Date: 9/16/2021

Test Information

Test Method: LM-41-14
Report Number: P582348
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2105-241-3)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/16/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC6W35D010SL-HM63040927-61NDW
Description: HALO COMMERCIAL 6" ROUND, NEW CONSTRUCTION FRAME, WITH 6" NARROW DISTRIBUTION, WHITE TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2795.2 lumens
Efficiency: N/A
Efficacy: 82.9 lumens/watt
Spacing Criteria (0/90/45): 1.06 / 1.06 / 1.03
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 33.7
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P582348
CATALOG NUMBER: HCC6W35D010SL-HM63040927-61NDW

Luminous Intensity Polar Plot





TEST NUMBER: P582348
 CATALOG NUMBER: HCC6W35D010SL-HM63040927-61NDW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10		0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	111	108	104	101	109	105	102	100	101	99	96	97	95	94	94	92	91	89		
2	104	97	92	87	101	95	90	86	92	88	84	89	85	83	86	83	81	79		
3	97	88	82	77	94	87	81	76	84	79	75	81	77	73	79	75	72	70		
4	90	81	73	68	88	79	73	68	77	71	67	75	70	66	73	69	65	63		
5	84	74	67	61	83	73	66	61	71	65	60	69	64	60	67	63	59	57		
6	79	68	61	55	77	67	60	55	66	59	55	64	59	54	63	58	54	52		
7	74	63	56	50	73	62	55	50	61	55	50	60	54	50	58	53	49	48		
8	70	59	51	46	69	58	51	46	57	50	46	56	50	46	54	49	46	44		
9	66	55	48	43	65	54	47	43	53	47	42	52	46	42	51	46	42	41		
10	63	51	44	40	61	51	44	40	50	44	39	49	43	39	48	43	39	38		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	105869
5°	105371
10°	103043
15°	100625
20°	96848
25°	91590
30°	83234
35°	67371
40°	45428
45°	31220
50°	25577
55°	22384
60°	21172
65°	19976
70°	18769
75°	17855
80°	16195
85°	14215



TEST NUMBER: P582348
 CATALOG NUMBER: HCC6W35D010SL-HM63040927-61NDW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	180.8	6.5
10°-20°	497.9	17.8
20°-30°	691.8	24.7
30°-40°	615.9	22.0
40°-50°	326.9	11.7
50°-60°	213.8	7.6
60°-70°	153.2	5.5
70°-80°	88.9	3.2
80°-90°	26.0	0.9
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1370.4	49.0
0°-40°	1986.3	71.1
0°-60°	2527.1	90.4
0°-90°	2795.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2795.2	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1931	
5°	1915	181
15°	1773	498
25°	1514	692
35°	1007	616
45°	403	327
55°	234	214
65°	154	153
75°	84	89
85°	23	26
90°	0	



TEST NUMBER: P582348
CATALOG NUMBER: HCC6W35D010SL-HM63040927-61NDW

CANDELA DISTRIBUTION (FULL):

	0°
0°	1931.2
2.5°	1920.9
5°	1914.8
7.5°	1892.2
10°	1851.1
12.5°	1814.1
15°	1773.0
17.5°	1721.7
20°	1660.1
22.5°	1590.2
25°	1514.2
27.5°	1425.8
30°	1314.9
32.5°	1181.4
35°	1006.7
37.5°	813.5
40°	634.8
42.5°	493.1
45°	402.7
47.5°	343.1
50°	299.9
52.5°	265.0
55°	234.2
57.5°	211.6
60°	193.1
62.5°	174.6
65°	154.0
67.5°	135.6
70°	117.1
72.5°	100.7
75°	84.3
77.5°	67.8
80°	51.3
82.5°	37.0
85°	22.6
87.5°	10.3
90°	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)