

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P582409

Luminaire Tested: **HCC6W35D010MB-HM63040940-61WDW**

Issue Date: 9/16/2021

Test Information

Test Method: LM-41-14
Report Number: P582409
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2105-241-9)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/16/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC6W35D010MB-HM63040940-61WDW
Description: HALO COMMERCIAL 6" ROUND, NEW CONSTRUCTION FRAME, WITH 6" WIDE DISTRIBUTION, WHITE TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 4000K CCT CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3622.4 lumens
Efficiency: N/A
Efficacy: 107.5 lumens/watt
Spacing Criteria (0/90/45): 1.11 / 1.11 / 1.09
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 33.7
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P582409
CATALOG NUMBER: HCC6W35D010MB-HM63040940-61WDW

Luminous Intensity Polar Plot





TEST NUMBER: P582409

CATALOG NUMBER: HCC6W35D010MB-HM63040940-61WDW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	111	107	104	101	108	105	102	99	101	98	96	97	95	93	94	92	90	89			
2	103	97	91	87	101	95	90	86	91	87	84	88	85	82	85	83	80	78			
3	96	87	81	76	94	86	80	75	83	78	74	81	76	72	78	74	71	69			
4	89	80	72	67	87	78	72	66	76	70	66	74	69	65	72	67	64	62			
5	84	73	65	60	82	72	65	59	70	64	59	68	63	58	66	61	58	56			
6	78	67	59	54	76	66	59	54	64	58	53	63	57	53	61	56	52	51			
7	73	62	54	49	72	61	54	49	60	53	48	58	52	48	57	52	48	46			
8	69	57	50	45	68	57	50	45	55	49	44	54	48	44	53	48	44	42			
9	65	53	46	41	64	53	46	41	52	45	41	51	45	41	50	44	41	39			
10	61	50	43	38	60	49	42	38	48	42	38	47	42	38	47	41	38	36			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	123614
5°	123541
10°	122348
15°	121079
20°	117657
25°	112688
30°	104579
35°	89978
40°	65680
45°	45005
50°	36178
55°	31531
60°	29099
65°	27668
70°	25854
75°	24167
80°	21909
85°	18744



TEST NUMBER: P582409
 CATALOG NUMBER: HCC6W35D010MB-HM63040940-61WDW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	212.8	5.9
10°-20°	599.2	16.5
20°-30°	852.1	23.5
30°-40°	820.4	22.6
40°-50°	472.0	13.0
50°-60°	299.1	8.3
60°-70°	211.7	5.8
70°-80°	120.7	3.3
80°-90°	34.4	0.9
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1664.1	45.9
0°-40°	2484.5	68.6
0°-60°	3255.6	89.9
0°-90°	3622.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3622.4	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2255	
5°	2245	213
15°	2133	599
25°	1863	852
35°	1344	820
45°	580	472
55°	330	299
65°	213	212
75°	114	121
85°	30	34
90°	0	



TEST NUMBER: P582409
CATALOG NUMBER: HCC6W35D010MB-HM63040940-61WDW

CANDELA DISTRIBUTION (FULL):

	0°
0°	2254.9
2.5°	2245.0
5°	2245.0
7.5°	2230.1
10°	2197.9
12.5°	2165.6
15°	2133.4
17.5°	2083.8
20°	2016.8
22.5°	1942.4
25°	1863.0
27.5°	1766.3
30°	1652.1
32.5°	1513.2
35°	1344.5
37.5°	1138.6
40°	917.8
42.5°	724.4
45°	580.5
47.5°	488.7
50°	424.2
52.5°	372.2
55°	329.9
57.5°	292.7
60°	265.4
62.5°	240.6
65°	213.3
67.5°	188.6
70°	161.3
72.5°	136.4
75°	114.1
77.5°	91.8
80°	69.4
82.5°	49.6
85°	29.8
87.5°	12.4
90°	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)