

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P582402

Luminaire Tested: **HCC6W35D010MW-HM63040940-61NDW**

Issue Date: 9/16/2021

Test Information

Test Method: LM-41-14
Report Number: P582402
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2105-241-3)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/16/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC6W35D010MW-HM63040940-61NDW
Description: HALO COMMERCIAL 6" ROUND, NEW CONSTRUCTION FRAME, WITH 6" NARROW DISTRIBUTION, WHITE TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 4000K CCT
CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3376.8 lumens
Efficiency: N/A
Efficacy: 100.2 lumens/watt
Spacing Criteria (0/90/45): 1.06 / 1.06 / 1.03
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 33.7
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P582402
CATALOG NUMBER: HCC6W35D010MW-HM63040940-61NDW

Luminous Intensity Polar Plot





TEST NUMBER: P582402

CATALOG NUMBER: HCC6W35D010MW-HM63040940-61NDW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	111	108	104	101	109	105	102	100	101	99	96	97	95	94	94	92	91	89			89
2	104	97	92	87	101	95	90	86	92	88	84	89	85	83	86	83	81	79			79
3	97	88	82	77	94	87	81	76	84	79	75	81	77	73	79	75	72	70			70
4	90	81	73	68	88	79	73	68	77	71	67	75	70	66	73	69	65	63			63
5	84	74	67	61	83	73	66	61	71	65	60	69	64	60	67	63	59	57			57
6	79	68	61	55	77	67	60	55	66	59	55	64	59	54	63	58	54	52			52
7	74	63	56	50	73	62	55	50	61	55	50	60	54	50	58	53	49	48			48
8	70	59	51	46	69	58	51	46	57	50	46	56	50	46	54	49	46	44			44
9	66	55	48	43	65	54	47	43	53	47	42	52	46	42	51	46	42	41			41
10	62	51	44	40	61	51	44	40	50	44	39	49	43	39	48	43	39	38			38

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	127901
5°	127294
10°	124486
15°	121561
20°	116998
25°	110650
30°	100553
35°	81385
40°	54889
45°	37717
50°	30907
55°	27048
60°	25579
65°	24140
70°	22664
75°	21562
80°	19605
85°	17171



TEST NUMBER: P582402
 CATALOG NUMBER: HCC6W35D010MW-HM63040940-61NDW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	218.4	6.5
10°-20°	601.5	17.8
20°-30°	835.7	24.7
30°-40°	744.0	22.0
40°-50°	395.0	11.7
50°-60°	258.3	7.7
60°-70°	185.1	5.5
70°-80°	107.3	3.2
80°-90°	31.4	0.9
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1655.6	49.0
0°-40°	2399.6	71.1
0°-60°	3053.0	90.4
0°-90°	3376.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3376.8	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2333	
5°	2313	218
15°	2142	602
25°	1829	836
35°	1216	744
45°	486	395
55°	283	258
65°	186	185
75°	102	107
85°	27	31
90°	0	



TEST NUMBER: P582402

CATALOG NUMBER: HCC6W35D010MW-HM63040940-61NDW

CANDELA DISTRIBUTION (FULL):

0°	
0°	2333.1
2.5°	2320.7
5°	2313.2
7.5°	2285.9
10°	2236.3
12.5°	2191.6
15°	2141.9
17.5°	2079.9
20°	2005.5
22.5°	1921.1
25°	1829.3
27.5°	1722.5
30°	1588.5
32.5°	1427.1
35°	1216.1
37.5°	982.8
40°	767.0
42.5°	595.6
45°	486.5
47.5°	414.5
50°	362.4
52.5°	320.2
55°	283.0
57.5°	255.7
60°	233.3
62.5°	211.0
65°	186.1
67.5°	163.8
70°	141.4
72.5°	121.6
75°	101.8
77.5°	81.9
80°	62.1
82.5°	44.7
85°	27.3
87.5°	12.4
90°	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)