

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P582403

Luminaire Tested: **HCC6W35D010MW-HM63040940-61PSMDW**

Issue Date: 9/16/2021

Test Information

Test Method: LM-41-14
Report Number: P582403
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2105-241-12)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/16/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC6W35D010MW-HM63040940-61PSMDW
Description: HALO COMMERCIAL 6" ROUND, NEW CONSTRUCTION FRAME, WITH 6" PLASTIC TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 4000K CCT
CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3513.3 lumens
Efficiency: N/A
Efficacy: 104.3 lumens/watt
Spacing Criteria (0/90/45): 1.09 / 1.09 / 1.04
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 33.7
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P582403
CATALOG NUMBER: HCC6W35D010MW-HM63040940-61PSMDW

Luminous Intensity Polar Plot





TEST NUMBER: P582403

CATALOG NUMBER: HCC6W35D010MW-HM63040940-61PSMDW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	111	107	104	101	108	105	102	99	101	98	96	97	95	93	93	92	90	88			
2	103	96	91	86	101	95	90	85	91	87	83	88	85	82	85	82	80	78			
3	96	87	81	75	94	86	80	75	83	78	73	80	76	72	78	74	71	69			
4	89	80	72	67	87	78	72	66	76	70	65	74	69	65	72	67	64	62			
5	84	73	65	60	82	72	65	59	70	64	59	68	63	58	66	62	58	56			
6	78	67	59	54	77	66	59	54	64	58	53	63	57	53	61	56	53	51			
7	73	62	54	49	72	61	54	49	60	53	49	58	53	48	57	52	48	46			
8	69	57	50	45	68	57	50	45	56	49	45	54	49	44	53	48	44	43			
9	65	53	46	41	64	53	46	41	52	46	41	51	45	41	50	45	41	39			
10	62	50	43	38	60	49	43	38	49	42	38	48	42	38	47	42	38	36			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	125571
5°	125236
10°	123361
15°	121408
20°	117418
25°	111835
30°	102111
35°	82215
40°	55411
45°	40407
50°	34924
55°	31540
60°	29932
65°	28317
70°	26655
75°	25248
80°	23519
85°	21889



TEST NUMBER: P582403

CATALOG NUMBER: HCC6W35D010MW-HM63040940-61PSMDW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	215.4	6.1
10°-20°	600.7	17.1
20°-30°	844.0	24.0
30°-40°	751.3	21.4
40°-50°	419.9	12.0
50°-60°	299.1	8.5
60°-70°	217.6	6.2
70°-80°	126.0	3.6
80°-90°	39.2	1.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1660.2	47.3
0°-40°	2411.5	68.6
0°-60°	3130.5	89.1
0°-90°	3513.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3513.3	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2291	
5°	2276	215
15°	2139	601
25°	1849	844
35°	1228	751
45°	521	420
55°	330	299
65°	218	218
75°	119	126
85°	35	39
90°	0	



TEST NUMBER: P582403

CATALOG NUMBER: HCC6W35D010MW-HM63040940-61PSMDW

CANDELA DISTRIBUTION (FULL):

	0°
0°	2290.6
2.5°	2280.7
5°	2275.8
7.5°	2255.9
10°	2216.1
12.5°	2178.9
15°	2139.2
17.5°	2084.6
20°	2012.7
22.5°	1933.3
25°	1848.9
27.5°	1744.7
30°	1613.1
32.5°	1444.4
35°	1228.5
37.5°	985.2
40°	774.3
42.5°	617.9
45°	521.2
47.5°	456.6
50°	409.5
52.5°	367.3
55°	330.0
57.5°	300.3
60°	273.0
62.5°	248.2
65°	218.3
67.5°	193.6
70°	166.3
72.5°	141.4
75°	119.2
77.5°	96.7
80°	74.5
82.5°	54.6
85°	34.8
87.5°	17.4
90°	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)