

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P582415

Luminaire Tested: **HCC6S40D010BZ-HM63040827-61MDC**

Issue Date: 9/16/2021

Test Information

Test Method: LM-41-14
Report Number: P582415
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2105-241-4)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/16/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC6S40D010BZ-HM63040827-61MDC
Description: HALO COMMERCIAL 6" ROUND, NEW CONSTRUCTION FRAME, WITH 6" MEDIUM DISTRIBUTION, SPECULAR TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 2700K CCT
CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4454.2 lumens
Efficiency: N/A
Efficacy: 108.6 lumens/watt
Spacing Criteria (0/90/45): 1.06 / 1.06 / 0.96
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 41
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P582415
CATALOG NUMBER: HCC6S40D010BZ-HM63040827-61MDC

Luminous Intensity Polar Plot





TEST NUMBER: P582415
 CATALOG NUMBER: HCC6S40D010BZ-HM63040827-61MDC

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20		
RC	80				70				50				30				10		
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10		
RCR																			
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102		100
1	114	111	108	106	111	109	106	104	105	103	101	101	99	98	97	96	95		94
2	108	103	99	96	106	101	98	95	98	95	93	95	93	91	92	90	89		87
3	102	96	91	87	100	95	90	86	92	88	85	90	86	84	87	85	82		81
4	97	90	84	80	95	89	83	79	86	82	79	84	81	78	83	79	77		75
5	92	84	78	74	91	83	78	73	81	76	73	80	75	72	78	74	72		70
6	88	79	73	68	86	78	72	68	76	71	68	75	71	67	74	70	67		65
7	83	74	68	64	82	73	68	63	72	67	63	71	66	63	70	66	62		61
8	79	70	63	59	78	69	63	59	68	63	59	67	62	59	66	62	58		57
9	75	66	60	56	74	65	59	55	64	59	55	63	58	55	62	58	55		54
10	72	62	56	52	71	61	56	52	61	55	52	60	55	52	59	55	52		50

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	211513
5°	214813
10°	227044
15°	252805
20°	262173
25°	215105
30°	150732
35°	102834
40°	53565
45°	18839
50°	8435
55°	2695
60°	1546
65°	1090
70°	914
75°	593
80°	0
85°	0



TEST NUMBER: P582415
 CATALOG NUMBER: HCC6S40D010BZ-HM63040827-61MDC

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	378.1	8.5
10°-20°	1252.7	28.1
20°-30°	1595.1	35.8
30°-40°	950.6	21.3
40°-50°	230.5	5.2
50°-60°	35.4	0.8
60°-70°	8.7	0.2
70°-80°	3.0	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3226.0	72.4
0°-40°	4176.6	93.8
0°-60°	4442.5	99.7
0°-90°	4454.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4454.2	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3858	
5°	3904	378
15°	4454	1253
25°	3556	1595
35°	1537	951
45°	243	231
55°	28	35
65°	8	9
75°	3	3
85°	0	0
90°	0	



TEST NUMBER: P582415
CATALOG NUMBER: HCC6S40D010BZ-HM63040827-61MDC

CANDELA DISTRIBUTION (FULL):

	0°
0°	3858.3
2.5°	3858.3
5°	3903.6
7.5°	3974.1
10°	4078.7
12.5°	4242.6
15°	4454.4
17.5°	4587.1
20°	4494.0
22.5°	4135.2
25°	3556.2
27.5°	2917.8
30°	2381.2
32.5°	1946.2
35°	1536.6
37.5°	1132.6
40°	748.5
42.5°	403.9
45°	243.0
47.5°	152.5
50°	98.9
52.5°	59.4
55°	28.2
57.5°	16.9
60°	14.1
62.5°	11.3
65°	8.4
67.5°	5.7
70°	5.7
72.5°	2.8
75°	2.8
77.5°	2.8
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)