

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P582425

Luminaire Tested: **HCC6W40D010MW-HM63040827-61WDC**

Issue Date: 9/16/2021

Test Information

Test Method: LM-41-14
Report Number: P582425
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2105-241-7)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/16/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC6W40D010MW-HM63040827-61WDC
Description: HALO COMMERCIAL 6" ROUND, NEW CONSTRUCTION FRAME, WITH 6" WIDE DISTRIBUTION, SPECULAR TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 2700K CCT
CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4555.8 lumens
Efficiency: N/A
Efficacy: 111.1 lumens/watt
Spacing Criteria (0/90/45): 1.28 / 1.28 / 1.09
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 41
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P582425
CATALOG NUMBER: HCC6W40D010MW-HM63040827-61WDC

Luminous Intensity Polar Plot





TEST NUMBER: P582425

CATALOG NUMBER: HCC6W40D010MW-HM63040827-61WDC

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	113	110	108	105	111	108	106	103	104	102	100	100	99	97	97	96	94	93				93
2	107	102	97	94	105	100	96	93	97	94	91	94	91	89	91	89	87	85				85
3	101	94	89	85	99	93	88	84	90	86	82	88	84	81	85	82	80	78				78
4	95	87	81	77	93	86	80	76	84	79	75	82	78	74	80	76	74	72				72
5	90	81	75	70	88	80	74	70	78	73	69	76	72	68	75	71	68	66				66
6	85	75	69	64	83	74	68	64	73	67	63	71	67	63	70	66	62	61				61
7	80	70	63	59	79	69	63	59	68	62	58	67	62	58	66	61	58	56				56
8	76	65	59	54	74	65	59	54	64	58	54	62	57	54	61	57	53	52				52
9	71	61	55	50	70	60	54	50	60	54	50	59	53	50	58	53	50	48				48
10	68	57	51	47	67	57	51	47	56	50	46	55	50	46	54	50	46	45				45

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	161517
5°	163685
10°	169825
15°	184683
20°	206489
25°	217337
30°	191327
35°	132708
40°	79241
45°	37671
50°	14217
55°	5935
60°	1853
65°	1466
70°	914
75°	593
80°	884
85°	0



TEST NUMBER: P582425
 CATALOG NUMBER: HCC6W40D010MW-HM63040827-61WDC

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	286.3	6.3
10°-20°	934.4	20.5
20°-30°	1601.2	35.1
30°-40°	1243.5	27.3
40°-50°	411.1	9.0
50°-60°	63.0	1.4
60°-70°	11.1	0.2
70°-80°	4.1	0.1
80°-90°	1.1	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2821.9	61.9
0°-40°	4065.3	89.2
0°-60°	4539.5	99.6
0°-90°	4555.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4555.8	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2946	
5°	2974	286
15°	3254	934
25°	3593	1601
35°	1983	1243
45°	486	411
55°	62	63
65°	11	11
75°	3	4
85°	0	1
90°	0	



TEST NUMBER: P582425
CATALOG NUMBER: HCC6W40D010MW-HM63040827-61WDC

CANDELA DISTRIBUTION (FULL):

	0°
0°	2946.3
2.5°	2943.5
5°	2974.5
7.5°	3008.4
10°	3050.8
12.5°	3135.5
15°	3254.1
17.5°	3398.3
20°	3539.5
22.5°	3621.4
25°	3593.1
27.5°	3398.3
30°	3022.5
32.5°	2516.9
35°	1983.0
37.5°	1505.6
40°	1107.3
42.5°	782.4
45°	485.9
47.5°	271.2
50°	166.7
52.5°	101.7
55°	62.1
57.5°	31.1
60°	16.9
62.5°	14.1
65°	11.3
67.5°	8.4
70°	5.7
72.5°	5.7
75°	2.8
77.5°	2.8
80°	2.8
82.5°	2.8
85°	0.0
87.5°	0.0
90°	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)