

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P582443

Luminaire Tested: **HCC6S40D010MB-HM63040830-61WDC**

Issue Date: 9/16/2021

**Test Information**

Test Method: LM-41-14  
Report Number: P582443  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2105-241-7)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 9/16/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: HALO COMMERCIAL  
Catalog Number: HCC6S40D010MB-HM63040830-61WDC  
Description: HALO COMMERCIAL 6" ROUND, NEW CONSTRUCTION FRAME, WITH 6" WIDE DISTRIBUTION, SPECULAR TRIM  
Light Source: (1) HIGH LUMEN LED 80CRI / 3000K CCT CYLINDER  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 4887.6 lumens  
Efficiency: N/A  
Efficacy: 119.2 lumens/watt  
Spacing Criteria (0/90/45): 1.28 / 1.28 / 1.09  
Luminous Opening: Circular (Dia: 0.5' x H: 0')  
CIE Type: Direct

Input Watts (W): 41  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P582443  
CATALOG NUMBER: HCC6S40D010MB-HM63040830-61WDC

### Luminous Intensity Polar Plot





TEST NUMBER: P582443  
 CATALOG NUMBER: HCC6S40D010MB-HM63040830-61WDC

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	113	110	108	105	111	108	106	103	104	102	100	100	99	97	97	96	94	93
2	107	102	97	94	105	100	96	93	97	94	91	94	91	89	91	89	87	85
3	101	94	89	85	99	93	88	84	90	86	82	88	84	81	85	82	80	78
4	95	87	81	77	93	86	80	76	84	79	75	82	78	74	80	76	74	72
5	90	81	75	70	88	80	74	70	78	73	69	76	72	68	75	71	68	66
6	85	75	69	64	83	74	68	64	73	67	63	71	67	63	70	66	62	61
7	80	70	63	59	79	69	63	59	68	62	58	67	62	58	66	61	58	56
8	76	65	59	54	74	65	59	54	64	58	54	62	57	54	61	57	53	52
9	71	61	55	50	70	60	54	50	60	54	50	59	53	50	58	53	50	48
10	68	57	51	47	67	57	51	47	56	50	46	55	50	46	54	50	46	45

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	173270
5°	175605
10°	182194
15°	198134
20°	221517
25°	233167
30°	205259
35°	142372
40°	85009
45°	40415
50°	15257
55°	6365
60°	1995
65°	1570
70°	978
75°	635
80°	947
85°	0



TEST NUMBER: P582443  
 CATALOG NUMBER: HCC6S40D010MB-HM63040830-61WDC

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	307.1	6.3
10°-20°	1002.5	20.5
20°-30°	1717.7	35.1
30°-40°	1334.0	27.3
40°-50°	441.0	9.0
50°-60°	67.7	1.4
60°-70°	12.0	0.2
70°-80°	4.4	0.1
80°-90°	1.2	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3027.3	61.9
0°-40°	4361.3	89.2
0°-60°	4870.0	99.6
0°-90°	4887.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4887.6	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	3161	
5°	3191	307
15°	3491	1002
25°	3855	1718
35°	2127	1334
45°	521	441
55°	67	68
65°	12	12
75°	3	4
85°	0	1
90°	0	



TEST NUMBER: P582443  
CATALOG NUMBER: HCC6S40D010MB-HM63040830-61WDC

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	3160.7
2.5°	3157.7
5°	3191.1
7.5°	3227.5
10°	3273.0
12.5°	3363.8
15°	3491.1
17.5°	3645.7
20°	3797.1
22.5°	3885.1
25°	3854.8
27.5°	3645.7
30°	3242.6
32.5°	2700.1
35°	2127.4
37.5°	1615.2
40°	1187.9
42.5°	839.4
45°	521.3
47.5°	291.0
50°	178.9
52.5°	109.1
55°	66.6
57.5°	33.4
60°	18.2
62.5°	15.2
65°	12.1
67.5°	9.1
70°	6.1
72.5°	6.1
75°	3.0
77.5°	3.0
80°	3.0
82.5°	3.0
85°	0.0
87.5°	0.0
90°	0.0

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)