

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P582463

Luminaire Tested: **HCC6W40D010BZ-HM63040835-61WDW**

Issue Date: 9/16/2021

**Test Information**

Test Method: LM-41-14  
Report Number: P582463  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2105-241-9)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 9/16/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: HALO COMMERCIAL  
Catalog Number: HCC6W40D010BZ-HM63040835-61WDW  
Description: HALO COMMERCIAL 6" ROUND, NEW CONSTRUCTION FRAME, WITH 6" WIDE DISTRIBUTION, WHITE TRIM  
Light Source: (1) HIGH LUMEN LED 80CRI / 3500K CCT  
CYLINDER  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 4590.9 lumens  
Efficiency: N/A  
Efficacy: 112.0 lumens/watt  
Spacing Criteria (0/90/45): 1.11 / 1.11 / 1.09  
Luminous Opening: Circular (Dia: 0.5' x H: 0')  
CIE Type: Direct

Input Watts (W): 41  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P582463  
CATALOG NUMBER: HCC6W40D010BZ-HM63040835-61WDW

### Luminous Intensity Polar Plot





TEST NUMBER: P582463  
 CATALOG NUMBER: HCC6W40D010BZ-HM63040835-61WDW

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20		
RC	80				70				50				30				10		0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10		0
RCR																			
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102		100
1	111	107	104	101	108	105	102	99	101	98	96	97	95	93	94	92	90		89
2	103	97	91	87	101	95	90	86	91	87	84	88	85	82	85	83	80		78
3	96	87	81	76	94	86	80	75	83	78	74	81	76	72	78	74	71		69
4	89	80	72	67	87	78	72	66	76	70	66	74	69	65	72	67	64		62
5	84	73	65	60	82	72	65	59	70	64	59	68	63	58	66	62	58		56
6	78	67	59	54	76	66	59	54	64	58	53	63	57	53	61	56	52		51
7	73	62	54	49	72	61	54	49	60	53	48	58	52	48	57	52	48		46
8	69	57	50	45	68	57	50	45	55	49	44	54	48	44	53	48	44		42
9	65	53	46	41	64	53	46	41	52	45	41	51	45	41	50	44	41		39
10	61	50	43	38	60	49	42	38	48	42	38	47	42	38	47	41	38		36

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	156660
5°	156570
10°	155057
15°	153452
20°	149113
25°	142811
30°	132539
35°	114037
40°	83242
45°	57037
50°	45849
55°	39960
60°	36872
65°	35075
70°	32746
75°	30628
80°	27781
85°	23713



TEST NUMBER: P582463  
 CATALOG NUMBER: HCC6W40D010BZ-HM63040835-61WDW

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	269.7	5.9
10°-20°	759.3	16.5
20°-30°	1079.9	23.5
30°-40°	1039.7	22.6
40°-50°	598.2	13.0
50°-60°	379.0	8.3
60°-70°	268.3	5.8
70°-80°	152.9	3.3
80°-90°	43.6	0.9
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2109.0	45.9
0°-40°	3148.7	68.6
0°-60°	4126.0	89.9
0°-90°	4590.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4590.9	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	2858	
5°	2845	270
15°	2704	759
25°	2361	1080
35°	1704	1040
45°	736	598
55°	418	379
65°	270	268
75°	145	153
85°	38	44
90°	0	



TEST NUMBER: P582463

CATALOG NUMBER: HCC6W40D010BZ-HM63040835-61WDW

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	2857.7
2.5°	2845.2
5°	2845.2
7.5°	2826.4
10°	2785.5
12.5°	2744.6
15°	2703.8
17.5°	2640.9
20°	2556.0
22.5°	2461.6
25°	2361.0
27.5°	2238.5
30°	2093.8
32.5°	1917.8
35°	1704.0
37.5°	1443.1
40°	1163.2
42.5°	918.0
45°	735.7
47.5°	619.4
50°	537.6
52.5°	471.5
55°	418.1
57.5°	371.0
60°	336.3
62.5°	305.0
65°	270.4
67.5°	239.0
70°	204.3
72.5°	172.9
75°	144.6
77.5°	116.3
80°	88.0
82.5°	62.9
85°	37.7
87.5°	15.7
90°	0.0

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)