

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P593271

Luminaire Tested: **HCC6S40D010MW-HM63040850-61NDH**

Issue Date: 9/16/2021

Test Information

Test Method: LM-41-14
Report Number: P593271
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2105-241-2)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/16/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC6S40D010MW-HM63040850-61NDH
Description: HALO COMMERCIAL 6" ROUND, NEW CONSTRUCTION FRAME, WITH 6" NARROW DISTRIBUTION, HAZE TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 5000K CCT
CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4797.3 lumens
Efficiency: N/A
Efficacy: 117.0 lumens/watt
Spacing Criteria (0/90/45): 0.89 / 0.89 / 0.89
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 41
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P593271
CATALOG NUMBER: HCC6S40D010MW-HM63040850-61NDH

Luminous Intensity Polar Plot





TEST NUMBER: P593271
 CATALOG NUMBER: HCC6S40D010MW-HM63040850-61NDH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	113	111	108	106	111	109	106	104	105	103	101		101	99	98		97	96	95	93
2	108	103	99	96	106	101	98	94	98	95	92		95	93	90		92	90	89	87
3	102	96	91	87	100	95	90	86	92	88	85		90	86	84		87	85	82	81
4	97	90	84	80	95	88	83	79	86	82	78		84	81	78		82	79	77	75
5	92	84	78	74	91	83	77	73	81	76	73		79	75	72		78	74	71	70
6	88	79	73	68	86	78	72	68	76	71	68		75	71	67		74	70	67	65
7	83	74	68	64	82	73	67	63	72	67	63		71	66	63		70	66	62	61
8	79	70	64	59	78	69	63	59	68	63	59		67	62	59		66	62	59	57
9	75	66	60	56	74	65	59	56	64	59	55		63	59	55		62	58	55	54
10	72	62	56	52	71	62	56	52	61	56	52		60	55	52		59	55	52	51

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	293672
5°	292427
10°	285505
15°	271017
20°	241574
25°	203492
30°	162120
35°	115670
40°	62195
45°	26646
50°	12119
55°	4425
60°	2171
65°	1712
70°	1587
75°	699
80°	1042
85°	0



TEST NUMBER: P593271
 CATALOG NUMBER: HCC6S40D010MW-HM63040850-61NDH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	501.6	10.5
10°-20°	1323.7	27.6
20°-30°	1533.1	32.0
30°-40°	1060.1	22.1
40°-50°	306.1	6.4
50°-60°	52.7	1.1
60°-70°	13.4	0.3
70°-80°	5.2	0.1
80°-90°	1.3	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3358.4	70.0
0°-40°	4418.5	92.1
0°-60°	4777.3	99.6
0°-90°	4797.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4797.3	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	5357	
5°	5314	502
15°	4775	1324
25°	3364	1533
35°	1728	1060
45°	344	306
55°	46	53
65°	13	13
75°	3	5
85°	0	1
90°	0	



TEST NUMBER: P593271
CATALOG NUMBER: HCC6S40D010MW-HM63040850-61NDH

CANDELA DISTRIBUTION (FULL):

	0°
0°	5357.0
2.5°	5333.8
5°	5314.0
7.5°	5254.5
10°	5128.9
12.5°	4976.9
15°	4775.3
17.5°	4491.1
20°	4140.9
22.5°	3754.1
25°	3364.2
27.5°	2964.3
30°	2561.1
32.5°	2158.0
35°	1728.4
37.5°	1282.2
40°	869.1
42.5°	548.6
45°	343.7
47.5°	221.5
50°	142.1
52.5°	85.9
55°	46.3
57.5°	26.4
60°	19.8
62.5°	16.5
65°	13.2
67.5°	9.9
70°	9.9
72.5°	6.6
75°	3.3
77.5°	3.3
80°	3.3
82.5°	3.3
85°	0.0
87.5°	0.0
90°	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)