

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P593272

Luminaire Tested: **HCC6S40D010MW-HM63040850-61WDH**

Issue Date: 9/16/2021

Test Information

Test Method: LM-41-14
Report Number: P593272
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2105-241-8)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/16/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC6S40D010MW-HM63040850-61WDH
Description: HALO COMMERCIAL 6" ROUND, NEW CONSTRUCTION FRAME, WITH 6" WIDE DISTRIBUTION, HAZE TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 5000K CCT CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4886.5 lumens
Efficiency: N/A
Efficacy: 119.2 lumens/watt
Spacing Criteria (0/90/45): 1.18 / 1.18 / 1.08
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 41
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P593272
CATALOG NUMBER: HCC6S40D010MW-HM63040850-61WDH

Luminous Intensity Polar Plot





TEST NUMBER: P593272
 CATALOG NUMBER: HCC6S40D010MW-HM63040850-61WDH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10		0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	113	110	107	105	110	108	105	103	103	101	100	100	98	97	96	95	94	92		
2	106	101	96	93	104	99	95	92	96	92	90	93	90	88	90	88	86	84		
3	100	93	87	83	98	91	86	82	89	84	81	86	83	80	84	81	78	77		
4	94	86	79	75	92	85	79	74	82	77	73	80	76	72	78	75	72	70		
5	89	79	73	68	87	78	72	68	76	71	67	75	70	66	73	69	66	64		
6	83	73	67	62	82	73	66	62	71	65	61	70	65	61	68	64	60	59		
7	79	68	62	57	77	68	61	57	66	60	56	65	60	56	64	59	56	54		
8	74	64	57	52	73	63	57	52	62	56	52	61	56	52	60	55	51	50		
9	70	59	53	48	69	59	53	48	58	52	48	57	52	48	56	51	48	46		
10	66	56	49	45	65	55	49	45	54	49	45	53	48	45	53	48	44	43		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	191377
5°	192653
10°	194881
15°	198877
20°	199990
25°	193759
30°	175780
35°	142921
40°	94863
45°	52796
50°	29611
55°	16430
60°	9067
65°	6862
70°	4776
75°	3495
80°	2084
85°	2076



TEST NUMBER: P593272
 CATALOG NUMBER: HCC6S40D010MW-HM63040850-61WDH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	334.1	6.8
10°-20°	988.1	20.2
20°-30°	1456.3	29.8
30°-40°	1302.5	26.7
40°-50°	565.1	11.6
50°-60°	166.1	3.4
60°-70°	53.0	1.1
70°-80°	18.7	0.4
80°-90°	2.7	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2778.5	56.9
0°-40°	4081.0	83.5
0°-60°	4812.1	98.5
0°-90°	4886.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4886.5	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3491	
5°	3501	334
15°	3504	988
25°	3203	1456
35°	2136	1303
45°	681	565
55°	172	166
65°	53	53
75°	16	19
85°	3	3
90°	0	



TEST NUMBER: P593272
CATALOG NUMBER: HCC6S40D010MW-HM63040850-61WDH

CANDELA DISTRIBUTION (FULL):

0°	
0°	3491.0
2.5°	3481.0
5°	3500.9
7.5°	3507.5
10°	3500.9
12.5°	3500.9
15°	3504.2
17.5°	3484.4
20°	3428.1
22.5°	3332.3
25°	3203.3
27.5°	3021.6
30°	2776.9
32.5°	2485.9
35°	2135.6
37.5°	1735.5
40°	1325.6
42.5°	968.5
45°	681.0
47.5°	485.9
50°	347.2
52.5°	248.0
55°	171.9
57.5°	115.7
60°	82.7
62.5°	66.1
65°	52.9
67.5°	39.7
70°	29.8
72.5°	23.1
75°	16.5
77.5°	13.2
80°	6.6
82.5°	3.3
85°	3.3
87.5°	0.0
90°	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)