

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P593280

Luminaire Tested: **HCC6W40D010SL-HM63040850-61WDW**

Issue Date: 9/16/2021

Test Information

Test Method: LM-41-14
Report Number: P593280
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2105-241-9)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/16/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC6W40D010SL-HM63040850-61WDW
Description: HALO COMMERCIAL 6" ROUND, NEW CONSTRUCTION FRAME, WITH 6" WIDE DISTRIBUTION, WHITE TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 5000K CCT CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4823.8 lumens
Efficiency: N/A
Efficacy: 117.7 lumens/watt
Spacing Criteria (0/90/45): 1.11 / 1.11 / 1.09
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 41
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P593280
CATALOG NUMBER: HCC6W40D010SL-HM63040850-61WDW

Luminous Intensity Polar Plot





TEST NUMBER: P593280
 CATALOG NUMBER: HCC6W40D010SL-HM63040850-61WDW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10		0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	111	107	104	101	108	105	102	99	101	98	96	97	95	93	94	92	90	89		
2	103	97	91	87	101	95	90	86	91	87	84	88	85	82	85	83	80	78		
3	96	87	81	76	94	86	80	75	83	78	74	81	76	72	78	74	71	69		
4	89	80	72	67	87	78	72	66	76	70	66	74	69	65	72	67	64	62		
5	84	73	65	60	82	72	65	59	70	64	59	68	63	58	66	61	58	56		
6	78	67	59	54	76	66	59	54	64	58	53	63	57	53	61	56	52	51		
7	73	62	54	49	72	61	54	49	60	53	48	58	52	48	57	52	48	46		
8	69	57	50	45	68	57	50	45	55	49	44	54	48	44	53	48	44	42		
9	65	53	46	41	64	53	46	41	52	45	41	51	45	41	50	44	41	39		
10	61	50	43	38	60	49	42	38	48	42	38	47	42	38	47	41	38	36		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	164609
5°	164511
10°	162917
15°	161232
20°	156674
25°	150057
30°	139268
35°	119819
40°	87464
45°	59921
50°	48178
55°	41996
60°	38758
65°	36852
70°	34413
75°	32174
80°	29202
85°	24971



TEST NUMBER: P593280
 CATALOG NUMBER: HCC6W40D010SL-HM63040850-61WDW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	283.4	5.9
10°-20°	797.9	16.5
20°-30°	1134.7	23.5
30°-40°	1092.4	22.6
40°-50°	628.6	13.0
50°-60°	398.3	8.3
60°-70°	281.9	5.8
70°-80°	160.7	3.3
80°-90°	45.8	1.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2216.0	45.9
0°-40°	3308.4	68.6
0°-60°	4335.3	89.9
0°-90°	4823.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4823.8	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3003	
5°	2990	283
15°	2841	798
25°	2481	1135
35°	1790	1092
45°	773	629
55°	439	398
65°	284	282
75°	152	161
85°	40	46
90°	0	



TEST NUMBER: P593280
CATALOG NUMBER: HCC6W40D010SL-HM63040850-61WDW

CANDELA DISTRIBUTION (FULL):

0°	
0°	3002.7
2.5°	2989.5
5°	2989.5
7.5°	2969.7
10°	2926.7
12.5°	2883.9
15°	2840.9
17.5°	2774.8
20°	2685.6
22.5°	2586.6
25°	2480.8
27.5°	2352.0
30°	2200.1
32.5°	2015.0
35°	1790.4
37.5°	1516.2
40°	1222.2
42.5°	964.6
45°	772.9
47.5°	650.8
50°	564.9
52.5°	495.5
55°	439.4
57.5°	389.8
60°	353.5
62.5°	320.4
65°	284.1
67.5°	251.0
70°	214.7
72.5°	181.6
75°	151.9
77.5°	122.3
80°	92.5
82.5°	66.1
85°	39.7
87.5°	16.5
90°	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)