

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P582499

Luminaire Tested: **HCC6S40D010MB-HM63040927-61WDW**

Issue Date: 9/16/2021

Test Information

Test Method: LM-41-14
Report Number: P582499
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2105-241-9)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/16/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC6S40D010MB-HM63040927-61WDW
Description: HALO COMMERCIAL 6" ROUND, NEW CONSTRUCTION FRAME, WITH 6" WIDE DISTRIBUTION, WHITE TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3481.9 lumens
Efficiency: N/A
Efficacy: 84.9 lumens/watt
Spacing Criteria (0/90/45): 1.11 / 1.11 / 1.09
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 41
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P582499
CATALOG NUMBER: HCC6S40D010MB-HM63040927-61WDW

Luminous Intensity Polar Plot





TEST NUMBER: P582499

CATALOG NUMBER: HCC6S40D010MB-HM63040927-61WDW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10		0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	111	107	104	101	108	105	102	99	101	98	96	97	95	93	94	92	90	89		
2	103	97	91	87	101	95	90	86	91	87	84	88	85	82	85	83	80	78		
3	96	87	81	76	94	86	80	75	83	78	74	81	76	72	78	74	71	69		
4	89	80	72	67	87	78	72	66	76	70	66	74	69	65	72	67	64	62		
5	84	73	65	60	82	72	65	59	70	64	59	68	63	58	66	62	58	56		
6	78	67	59	54	76	66	59	54	64	58	53	63	57	53	61	56	52	51		
7	73	62	54	49	72	61	54	49	60	53	48	58	52	48	57	52	48	46		
8	69	57	50	45	68	57	50	45	55	49	44	54	48	44	53	48	44	42		
9	65	53	46	41	64	53	46	41	52	45	41	51	45	41	50	44	41	39		
10	61	50	43	38	60	49	42	38	48	42	38	47	42	38	47	41	38	36		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	118817
5°	118748
10°	117600
15°	116380
20°	113089
25°	108315
30°	100528
35°	86491
40°	63140
45°	43253
50°	34771
55°	30307
60°	27969
65°	26605
70°	24844
75°	23235
80°	21057
85°	17989



TEST NUMBER: P582499
 CATALOG NUMBER: HCC6S40D010MB-HM63040927-61WDW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	204.6	5.9
10°-20°	575.9	16.5
20°-30°	819.1	23.5
30°-40°	788.6	22.6
40°-50°	453.7	13.0
50°-60°	287.5	8.3
60°-70°	203.5	5.8
70°-80°	116.0	3.3
80°-90°	33.1	0.9
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1599.5	45.9
0°-40°	2388.1	68.6
0°-60°	3129.3	89.9
0°-90°	3481.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3481.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2167	
5°	2158	205
15°	2051	576
25°	1791	819
35°	1292	789
45°	558	454
55°	317	287
65°	205	204
75°	110	116
85°	29	33
90°	0	



TEST NUMBER: P582499
CATALOG NUMBER: HCC6S40D010MB-HM63040927-61WDW

CANDELA DISTRIBUTION (FULL):

	0°
0°	2167.4
2.5°	2157.9
5°	2157.9
7.5°	2143.6
10°	2112.6
12.5°	2081.6
15°	2050.6
17.5°	2002.9
20°	1938.5
22.5°	1867.0
25°	1790.7
27.5°	1697.7
30°	1588.1
32.5°	1454.5
35°	1292.4
37.5°	1094.5
40°	882.3
42.5°	696.3
45°	557.9
47.5°	469.7
50°	407.7
52.5°	357.7
55°	317.1
57.5°	281.3
60°	255.1
62.5°	231.4
65°	205.1
67.5°	181.2
70°	155.0
72.5°	131.1
75°	109.7
77.5°	88.2
80°	66.7
82.5°	47.7
85°	28.6
87.5°	11.9
90°	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)