

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P582500

Luminaire Tested: **HCC6W40D010SL-HM63040927-61WDWB**

Issue Date: 9/16/2021

Test Information

Test Method: LM-41-14
Report Number: P582500
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2105-241-10)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/16/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC6W40D010SL-HM63040927-61WDWB
Description: HALO COMMERCIAL 6" ROUND, NEW CONSTRUCTION FRAME, WITH 6" WIDE DISTRIBUTION, WHITE BAFFLE TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3751.3 lumens
Efficiency: N/A
Efficacy: 91.5 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.2 / 1.05
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 41
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P582500
CATALOG NUMBER: HCC6W40D010SL-HM63040927-61WDWB

Luminous Intensity Polar Plot





TEST NUMBER: P582500

CATALOG NUMBER: HCC6W40D010SL-HM63040927-61WDWB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	112	109	106	103	110	107	104	102	103	100	98	99	97	95	95	94	93	91			91
2	106	100	95	91	103	98	94	90	95	91	88	92	89	86	89	86	84	82			82
3	99	92	86	81	97	90	85	81	88	83	79	85	81	78	83	80	77	75			75
4	93	85	78	73	91	83	78	73	81	76	72	79	75	71	77	73	70	69			69
5	88	78	72	67	86	77	71	66	75	70	66	74	69	65	72	68	65	63			63
6	83	73	66	61	81	72	66	61	70	65	60	69	64	60	67	63	60	58			58
7	78	68	61	56	77	67	61	56	66	60	56	64	59	55	63	59	55	54			54
8	74	63	57	52	73	63	56	52	61	56	52	60	55	51	59	55	51	50			50
9	70	59	53	48	69	59	52	48	58	52	48	57	51	48	56	51	48	46			46
10	66	56	49	45	65	55	49	45	54	48	45	53	48	44	53	48	44	43			43

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	139918
5°	141101
10°	146184
15°	158792
20°	165179
25°	157987
30°	136344
35°	98176
40°	55304
45°	28662
50°	17091
55°	12320
60°	10460
65°	12064
70°	15291
75°	16182
80°	15816
85°	15033



TEST NUMBER: P582500
 CATALOG NUMBER: HCC6W40D010SL-HM63040927-61WDWB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	246.7	6.6
10°-20°	789.1	21.0
20°-30°	1179.5	31.4
30°-40°	901.6	24.0
40°-50°	314.9	8.4
50°-60°	120.1	3.2
60°-70°	94.1	2.5
70°-80°	79.6	2.1
80°-90°	25.6	0.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2215.4	59.1
0°-40°	3117.0	83.1
0°-60°	3552.0	94.7
0°-90°	3751.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3751.3	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2552	
5°	2564	247
15°	2798	789
25°	2612	1180
35°	1467	902
45°	370	315
55°	129	120
65°	93	94
75°	76	80
85°	24	26
90°	0	



TEST NUMBER: P582500
CATALOG NUMBER: HCC6W40D010SL-HM63040927-61WDWB

CANDELA DISTRIBUTION (FULL):

	0°
0°	2552.3
2.5°	2545.1
5°	2564.1
7.5°	2590.4
10°	2626.1
12.5°	2707.2
15°	2797.9
17.5°	2852.7
20°	2831.4
22.5°	2745.5
25°	2611.9
27.5°	2421.0
30°	2153.9
32.5°	1834.3
35°	1467.0
37.5°	1087.6
40°	772.8
42.5°	541.4
45°	369.7
47.5°	260.0
50°	200.4
52.5°	157.5
55°	128.9
57.5°	105.0
60°	95.4
62.5°	93.0
65°	93.0
67.5°	97.7
70°	95.4
72.5°	88.2
75°	76.4
77.5°	64.4
80°	50.1
82.5°	35.7
85°	23.9
87.5°	9.5
90°	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)