

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P582534

Luminaire Tested: **HCC6W40D010MB-HM63040935-61WDH**

Issue Date: 9/16/2021

Test Information

Test Method: LM-41-14
Report Number: P582534
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2105-241-8)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/16/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC6W40D010MB-HM63040935-61WDH
Description: HALO COMMERCIAL 6" ROUND, NEW CONSTRUCTION FRAME, WITH 6" WIDE DISTRIBUTION, HAZE TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT
CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4154.2 lumens
Efficiency: N/A
Efficacy: 101.3 lumens/watt
Spacing Criteria (0/90/45): 1.18 / 1.18 / 1.08
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 41
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P582534
CATALOG NUMBER: HCC6W40D010MB-HM63040935-61WDH

Luminous Intensity Polar Plot





TEST NUMBER: P582534
 CATALOG NUMBER: HCC6W40D010MB-HM63040935-61WDH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	113	110	107	105	110	108	105	103	103	101	100	100	98	97	96	95	94	92			92
2	106	101	96	93	104	99	95	92	96	92	90	93	90	88	90	88	86	84			84
3	100	93	87	83	98	91	86	82	89	84	81	86	83	80	84	81	78	77			77
4	94	86	79	75	92	85	79	74	82	77	73	80	76	72	78	75	72	70			70
5	89	79	73	68	87	78	72	68	76	71	67	75	70	66	73	69	66	64			64
6	83	73	67	62	82	73	66	62	71	65	61	70	65	61	68	64	60	59			59
7	79	68	62	57	77	68	61	57	66	60	56	65	60	56	64	59	56	54			54
8	74	64	57	52	73	63	57	52	62	56	52	61	56	52	60	55	51	50			50
9	70	59	53	48	69	59	53	48	58	52	48	57	52	48	56	51	48	46			46
10	66	56	49	45	65	55	49	45	54	49	45	53	48	45	53	48	44	43			43

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	162695
5°	163774
10°	165667
15°	169070
20°	170016
25°	164719
30°	149428
35°	121499
40°	80651
45°	44881
50°	25168
55°	13964
60°	7708
65°	5837
70°	4055
75°	2987
80°	1799
85°	1761



TEST NUMBER: P582534
 CATALOG NUMBER: HCC6W40D010MB-HM63040935-61WDH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	284.1	6.8
10°-20°	840.0	20.2
20°-30°	1238.0	29.8
30°-40°	1107.3	26.7
40°-50°	480.4	11.6
50°-60°	141.2	3.4
60°-70°	45.1	1.1
70°-80°	15.9	0.4
80°-90°	2.3	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2362.0	56.9
0°-40°	3469.3	83.5
0°-60°	4090.9	98.5
0°-90°	4154.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4154.2	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2968	
5°	2976	284
15°	2979	840
25°	2723	1238
35°	1816	1107
45°	579	480
55°	146	141
65°	45	45
75°	14	16
85°	3	2
90°	0	



TEST NUMBER: P582534
CATALOG NUMBER: HCC6W40D010MB-HM63040935-61WDH

CANDELA DISTRIBUTION (FULL):

	0°
0°	2967.8
2.5°	2959.3
5°	2976.1
7.5°	2981.7
10°	2976.1
12.5°	2976.1
15°	2979.0
17.5°	2962.1
20°	2914.3
22.5°	2832.8
25°	2723.2
27.5°	2568.6
30°	2360.6
32.5°	2113.3
35°	1815.5
37.5°	1475.4
40°	1127.0
42.5°	823.5
45°	578.9
47.5°	413.1
50°	295.1
52.5°	210.8
55°	146.1
57.5°	98.4
60°	70.3
62.5°	56.2
65°	45.0
67.5°	33.8
70°	25.3
72.5°	19.7
75°	14.1
77.5°	11.2
80°	5.7
82.5°	2.8
85°	2.8
87.5°	0.0
90°	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)