

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P582535

Luminaire Tested: **HCC6S40D010SL-HM63040935-61WDW**

Issue Date: 9/16/2021

Test Information

Test Method: LM-41-14
Report Number: P582535
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2105-241-9)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/16/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC6S40D010SL-HM63040935-61WDW
Description: HALO COMMERCIAL 6" ROUND, NEW CONSTRUCTION FRAME, WITH 6" WIDE DISTRIBUTION, WHITE TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4100.6 lumens
Efficiency: N/A
Efficacy: 100.0 lumens/watt
Spacing Criteria (0/90/45): 1.11 / 1.11 / 1.09
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 41
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P582535
CATALOG NUMBER: HCC6S40D010SL-HM63040935-61WDW

Luminous Intensity Polar Plot





TEST NUMBER: P582535

CATALOG NUMBER: HCC6S40D010SL-HM63040935-61WDW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	111	107	104	101	108	105	102	99	101	98	96	97	95	93	94	92	90	89			
2	103	97	91	87	101	95	90	86	91	87	84	88	85	82	85	83	80	78			
3	96	87	81	76	94	86	80	75	83	78	74	81	76	72	78	74	71	69			
4	89	80	72	67	87	78	72	66	76	70	66	74	69	65	72	67	64	62			
5	84	73	65	60	82	72	65	59	70	64	59	68	63	58	66	62	58	56			
6	78	67	59	54	76	66	59	54	64	58	53	63	57	53	61	56	52	51			
7	73	62	54	49	72	61	54	49	60	53	48	58	52	48	57	52	48	46			
8	69	57	50	45	68	57	50	45	55	49	44	54	48	44	53	48	44	42			
9	65	53	46	41	64	53	46	41	52	45	41	51	45	41	50	44	41	39			
10	61	50	43	38	60	49	42	38	48	42	38	47	42	38	47	41	38	36			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	139939
5°	139852
10°	138497
15°	137067
20°	133192
25°	127562
30°	118385
35°	101857
40°	74354
45°	50943
50°	40954
55°	35698
60°	32947
65°	31326
70°	29252
75°	27345
80°	24814
85°	21134



TEST NUMBER: P582535
 CATALOG NUMBER: HCC6S40D010SL-HM63040935-61WDW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	240.9	5.9
10°-20°	678.3	16.5
20°-30°	964.6	23.5
30°-40°	928.7	22.6
40°-50°	534.3	13.0
50°-60°	338.6	8.3
60°-70°	239.7	5.8
70°-80°	136.6	3.3
80°-90°	38.9	0.9
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1883.8	45.9
0°-40°	2812.5	68.6
0°-60°	3685.4	89.9
0°-90°	4100.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4100.6	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2553	
5°	2541	241
15°	2415	678
25°	2109	965
35°	1522	929
45°	657	534
55°	374	339
65°	242	240
75°	129	137
85°	34	39
90°	0	



TEST NUMBER: P582535
CATALOG NUMBER: HCC6S40D010SL-HM63040935-61WDW

CANDELA DISTRIBUTION (FULL):

	0°
0°	2552.7
2.5°	2541.4
5°	2541.4
7.5°	2524.6
10°	2488.0
12.5°	2451.6
15°	2415.1
17.5°	2358.9
20°	2283.1
22.5°	2198.8
25°	2108.9
27.5°	1999.5
30°	1870.2
32.5°	1713.0
35°	1522.0
37.5°	1288.9
40°	1039.0
42.5°	820.0
45°	657.1
47.5°	553.2
50°	480.2
52.5°	421.3
55°	373.5
57.5°	331.3
60°	300.5
62.5°	272.4
65°	241.5
67.5°	213.4
70°	182.5
72.5°	154.5
75°	129.1
77.5°	103.9
80°	78.6
82.5°	56.2
85°	33.6
87.5°	14.0
90°	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)