

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P582529

Luminaire Tested: **HCC6W40D010BZ-HM63040935-61PSMDW**

Issue Date: 9/16/2021

Test Information

Test Method: LM-41-14
Report Number: P582529
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2105-241-12)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/16/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC6W40D010BZ-HM63040935-61PSMDW
Description: HALO COMMERCIAL 6" ROUND, NEW CONSTRUCTION FRAME, WITH 6" PLASTIC TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT
CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3977.1 lumens
Efficiency: N/A
Efficacy: 97.0 lumens/watt
Spacing Criteria (0/90/45): 1.09 / 1.09 / 1.04
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 41
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P582529
CATALOG NUMBER: HCC6W40D010BZ-HM63040935-61PSMDW

Luminous Intensity Polar Plot





TEST NUMBER: P582529

CATALOG NUMBER: HCC6W40D010BZ-HM63040935-61PSMDW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	111	107	104	101	108	105	102	99	101	98	96	97	95	93	93	92	90	88				88
2	103	96	91	86	101	95	90	85	91	87	83	88	85	82	85	82	80	78				78
3	96	87	81	75	94	86	80	75	83	78	73	80	76	72	78	74	71	69				69
4	89	80	72	67	87	78	72	66	76	70	65	74	69	65	72	67	64	62				62
5	84	73	65	60	82	72	65	59	70	64	59	68	63	58	66	62	58	56				56
6	78	67	59	54	77	66	59	54	64	58	53	63	57	53	61	56	53	51				51
7	73	62	54	49	72	61	54	49	60	53	49	58	53	48	57	52	48	46				46
8	69	57	50	45	68	57	50	45	56	49	45	54	49	44	53	48	44	43				43
9	65	53	46	41	64	53	46	41	52	46	41	51	45	41	50	45	41	39				39
10	62	50	43	38	60	49	43	38	49	42	38	48	42	38	47	42	38	36				36

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	142149
5°	141773
10°	139649
15°	137441
20°	132918
25°	126600
30°	115600
35°	93063
40°	62725
45°	45741
50°	39530
55°	35717
60°	33879
65°	32066
70°	30165
75°	28552
80°	26613
85°	24719



TEST NUMBER: P582529
 CATALOG NUMBER: HCC6W40D010BZ-HM63040935-61PSMDW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	243.8	6.1
10°-20°	680.1	17.1
20°-30°	955.5	24.0
30°-40°	850.5	21.4
40°-50°	475.3	12.0
50°-60°	338.6	8.5
60°-70°	246.3	6.2
70°-80°	142.6	3.6
80°-90°	44.4	1.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1879.4	47.3
0°-40°	2729.9	68.6
0°-60°	3543.8	89.1
0°-90°	3977.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3977.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2593	
5°	2576	244
15°	2422	680
25°	2093	955
35°	1391	850
45°	590	475
55°	374	339
65°	247	246
75°	135	143
85°	39	44
90°	0	



TEST NUMBER: P582529
CATALOG NUMBER: HCC6W40D010BZ-HM63040935-61PSMDW

CANDELA DISTRIBUTION (FULL):

	0°
0°	2593.0
2.5°	2581.8
5°	2576.3
7.5°	2553.7
10°	2508.7
12.5°	2466.7
15°	2421.7
17.5°	2360.0
20°	2278.4
22.5°	2188.5
25°	2093.0
27.5°	1974.9
30°	1826.2
32.5°	1635.0
35°	1390.6
37.5°	1115.3
40°	876.5
42.5°	699.6
45°	590.0
47.5°	516.9
50°	463.5
52.5°	415.7
55°	373.7
57.5°	339.9
60°	309.0
62.5°	280.9
65°	247.2
67.5°	219.1
70°	188.2
72.5°	160.1
75°	134.8
77.5°	109.6
80°	84.3
82.5°	61.9
85°	39.3
87.5°	19.7
90°	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)