

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P582525

Luminaire Tested: **HCC6W40D010MB-HM63040935-61MDW**

Issue Date: 9/16/2021

**Test Information**

Test Method: LM-41-14  
Report Number: P582525  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2105-241-6)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 9/16/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: HALO COMMERCIAL  
Catalog Number: HCC6W40D010MB-HM63040935-61MDW  
Description: HALO COMMERCIAL 6" ROUND, NEW CONSTRUCTION FRAME, WITH 6" MEDIUM DISTRIBUTION, WHITE TRIM  
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT CYLINDER  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 3878.8 lumens  
Efficiency: N/A  
Efficacy: 94.6 lumens/watt  
Spacing Criteria (0/90/45): 1.08 / 1.08 / 1.03  
Luminous Opening: Circular (Dia: 0.5' x H: 0')  
CIE Type: Direct

Input Watts (W): 41  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P582525  
CATALOG NUMBER: HCC6W40D010MB-HM63040935-61MDW

### Luminous Intensity Polar Plot





TEST NUMBER: P582525  
 CATALOG NUMBER: HCC6W40D010MB-HM63040935-61MDW

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	111	108	104	101	109	105	102	100	101	99	96	97	95	94	94	92	91	89
2	104	97	92	87	101	95	90	86	92	88	84	89	85	82	86	83	81	79
3	97	88	82	76	94	87	81	76	84	79	75	81	77	73	79	75	72	70
4	90	80	73	68	88	79	73	67	77	71	67	75	70	66	73	68	65	63
5	84	74	66	61	82	73	66	61	71	65	60	69	64	59	67	63	59	57
6	79	68	61	55	77	67	60	55	65	59	55	64	58	54	62	58	54	52
7	74	63	55	50	73	62	55	50	61	54	50	59	54	50	58	53	49	48
8	70	58	51	46	69	58	51	46	57	50	46	55	50	46	54	49	45	44
9	66	54	47	43	65	54	47	42	53	47	42	52	46	42	51	46	42	40
10	62	51	44	39	61	50	44	39	49	43	39	49	43	39	48	43	39	37

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	144391
5°	143864
10°	141464
15°	138968
20°	134167
25°	127223
30°	115714
35°	92454
40°	61694
45°	43974
50°	36638
55°	31932
60°	30162
65°	28421
70°	26110
75°	24379
80°	22162
85°	19436



TEST NUMBER: P582525  
 CATALOG NUMBER: HCC6W40D010MB-HM63040935-61MDW

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	247.3	6.4
10°-20°	687.5	17.7
20°-30°	960.8	24.8
30°-40°	846.3	21.8
40°-50°	457.2	11.8
50°-60°	305.7	7.9
60°-70°	216.7	5.6
70°-80°	121.8	3.1
80°-90°	35.5	0.9
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1895.5	48.9
0°-40°	2741.9	70.7
0°-60°	3504.8	90.4
0°-90°	3878.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3878.8	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	2634	
5°	2614	247
15°	2449	688
25°	2103	961
35°	1382	846
45°	567	457
55°	334	306
65°	219	217
75°	115	122
85°	31	36
90°	0	



TEST NUMBER: P582525  
CATALOG NUMBER: HCC6W40D010MB-HM63040935-61MDW

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	2633.9
2.5°	2619.9
5°	2614.3
7.5°	2589.1
10°	2541.3
12.5°	2496.3
15°	2448.6
17.5°	2384.1
20°	2299.8
22.5°	2207.1
25°	2103.3
27.5°	1982.5
30°	1828.0
32.5°	1637.1
35°	1381.5
37.5°	1103.6
40°	862.1
42.5°	679.5
45°	567.2
47.5°	491.5
50°	429.6
52.5°	379.1
55°	334.1
57.5°	303.2
60°	275.1
62.5°	247.0
65°	219.1
67.5°	191.0
70°	162.9
72.5°	137.6
75°	115.1
77.5°	92.7
80°	70.2
82.5°	50.5
85°	30.9
87.5°	14.0
90°	0.0

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)