

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P582577

Luminaire Tested: **HCC6W45D010MW-HM64560830-61MDC**

Issue Date: 9/16/2021

**Test Information**

Test Method: LM-41-14  
Report Number: P582577  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2105-241-4)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 9/16/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: HALO COMMERCIAL  
Catalog Number: HCC6W45D010MW-HM64560830-61MDC  
Description: HALO COMMERCIAL 6" ROUND, NEW CONSTRUCTION FRAME, WITH 6" MEDIUM DISTRIBUTION, SPECULAR TRIM  
Light Source: (1) HIGH LUMEN LED 80CRI / 3000K CCT  
CYLINDER  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 5196.2 lumens  
Efficiency: N/A  
Efficacy: 118.1 lumens/watt  
Spacing Criteria (0/90/45): 1.06 / 1.06 / 0.96  
Luminous Opening: Circular (Dia: 0.5' x H: 0')  
CIE Type: Direct

Input Watts (W): 44  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P582577  
CATALOG NUMBER: HCC6W45D010MW-HM64560830-61MDC

### Luminous Intensity Polar Plot





TEST NUMBER: P582577  
 CATALOG NUMBER: HCC6W45D010MW-HM64560830-61MDC

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	114	111	108	106	111	109	106	104	105	103	101	101	99	98	97	96	95	94
2	108	103	99	96	106	101	98	95	98	95	93	95	93	91	92	90	89	87
3	102	96	91	87	100	95	90	86	92	88	85	90	86	84	87	85	82	81
4	97	90	84	80	95	89	83	79	86	82	79	84	81	78	83	79	77	75
5	92	84	78	74	91	83	78	73	81	76	73	80	75	72	78	74	72	70
6	88	79	73	68	86	78	72	68	76	71	68	75	71	67	74	70	67	65
7	83	74	68	64	82	73	68	63	72	67	63	71	66	63	70	66	62	61
8	79	70	63	59	78	69	63	59	68	63	59	67	62	59	66	62	58	57
9	75	66	60	56	74	65	59	55	64	59	55	63	58	55	62	58	55	54
10	72	62	56	52	71	61	56	52	61	55	52	60	55	52	59	55	52	50

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	246757
5°	250599
10°	264869
15°	294922
20°	305845
25°	250932
30°	175837
35°	119966
40°	62489
45°	21971
50°	9833
55°	3154
60°	1798
65°	1284
70°	1058
75°	699
80°	0
85°	0



TEST NUMBER: P582577  
 CATALOG NUMBER: HCC6W45D010MW-HM64560830-61MDC

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	441.1	8.5
10°-20°	1461.4	28.1
20°-30°	1860.8	35.8
30°-40°	1109.0	21.3
40°-50°	268.9	5.2
50°-60°	41.3	0.8
60°-70°	10.1	0.2
70°-80°	3.5	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3763.4	72.4
0°-40°	4872.4	93.8
0°-60°	5182.6	99.7
0°-90°	5196.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5196.2	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	4501	
5°	4554	441
15°	5196	1461
25°	4148	1861
35°	1793	1109
45°	283	269
55°	33	41
65°	10	10
75°	3	3
85°	0	0
90°	0	



TEST NUMBER: P582577  
CATALOG NUMBER: HCC6W45D010MW-HM64560830-61MDC

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	4501.2
2.5°	4501.2
5°	4553.9
7.5°	4636.3
10°	4758.2
12.5°	4949.4
15°	5196.5
17.5°	5351.3
20°	5242.6
22.5°	4824.1
25°	4148.5
27.5°	3403.9
30°	2777.8
32.5°	2270.3
35°	1792.6
37.5°	1321.4
40°	873.2
42.5°	471.2
45°	283.4
47.5°	177.9
50°	115.3
52.5°	69.2
55°	33.0
57.5°	19.8
60°	16.4
62.5°	13.1
65°	9.9
67.5°	6.6
70°	6.6
72.5°	3.3
75°	3.3
77.5°	3.3
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)