

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P582582

Luminaire Tested: **HCC6S45D010SL-HM64560830-61NDW**

Issue Date: 9/16/2021

Test Information

Test Method: LM-41-14
Report Number: P582582
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2105-241-3)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/16/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC6S45D010SL-HM64560830-61NDW
Description: HALO COMMERCIAL 6" ROUND, NEW CONSTRUCTION FRAME, WITH 6" NARROW DISTRIBUTION, WHITE TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 3000K CCT
CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4484.6 lumens
Efficiency: N/A
Efficacy: 101.9 lumens/watt
Spacing Criteria (0/90/45): 1.06 / 1.06 / 1.03
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 44
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P582582
CATALOG NUMBER: HCC6S45D010SL-HM64560830-61NDW

Luminous Intensity Polar Plot





TEST NUMBER: P582582
 CATALOG NUMBER: HCC6S45D010SL-HM64560830-61NDW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	111	108	104	101	109	105	102	100	101	99	96	97	95	94	94	92	91	89
2	104	97	92	87	101	95	90	86	92	88	84	89	85	83	86	83	81	79
3	97	88	82	77	94	87	81	76	84	79	75	81	77	73	79	75	72	70
4	90	81	73	68	88	79	73	68	77	71	67	75	70	66	73	69	65	63
5	84	74	67	61	83	73	66	61	71	65	60	69	64	60	67	63	59	57
6	79	68	61	55	77	67	60	55	66	59	55	64	59	54	63	58	54	52
7	74	63	56	50	73	62	55	50	61	55	50	60	54	50	58	53	49	48
8	70	59	51	46	69	58	51	46	57	50	46	56	50	46	54	49	46	44
9	66	55	48	43	65	54	47	43	53	47	42	52	46	42	51	46	42	41
10	62	51	44	40	61	51	44	40	50	44	39	49	43	39	48	43	39	38

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	169855
5°	169051
10°	165316
15°	161442
20°	155373
25°	146942
30°	133533
35°	108087
40°	72887
45°	50090
50°	41048
55°	35908
60°	33967
65°	32079
70°	30117
75°	28615
80°	26045
85°	22769



TEST NUMBER: P582582
 CATALOG NUMBER: HCC6S45D010SL-HM64560830-61NDW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	290.0	6.5
10°-20°	798.8	17.8
20°-30°	1109.8	24.7
30°-40°	988.1	22.0
40°-50°	524.6	11.7
50°-60°	343.0	7.6
60°-70°	245.9	5.5
70°-80°	142.5	3.2
80°-90°	41.7	0.9
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2198.7	49.0
0°-40°	3186.8	71.1
0°-60°	4054.4	90.4
0°-90°	4484.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4484.6	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3098	
5°	3072	290
15°	2845	799
25°	2429	1110
35°	1615	988
45°	646	525
55°	376	343
65°	247	246
75°	135	143
85°	36	42
90°	0	



TEST NUMBER: P582582
CATALOG NUMBER: HCC6S45D010SL-HM64560830-61NDW

CANDELA DISTRIBUTION (FULL):

	0°
0°	3098.4
2.5°	3081.9
5°	3072.0
7.5°	3035.7
10°	2969.8
12.5°	2910.6
15°	2844.6
17.5°	2762.2
20°	2663.3
22.5°	2551.3
25°	2429.3
27.5°	2287.6
30°	2109.5
32.5°	1895.3
35°	1615.1
37.5°	1305.3
40°	1018.5
42.5°	791.1
45°	646.1
47.5°	550.5
50°	481.3
52.5°	425.2
55°	375.7
57.5°	339.5
60°	309.8
62.5°	280.2
65°	247.3
67.5°	217.6
70°	187.9
72.5°	161.5
75°	135.1
77.5°	108.7
80°	82.5
82.5°	59.4
85°	36.2
87.5°	16.5
90°	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)