

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P582583

Luminaire Tested: **HCC6W45D010MW-HM64560830-61PSMDW**

Issue Date: 9/16/2021

Test Information

Test Method: LM-41-14
Report Number: P582583
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2105-241-12)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/16/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC6W45D010MW-HM64560830-61PSMDW
Description: HALO COMMERCIAL 6" ROUND, NEW CONSTRUCTION FRAME, WITH 6" PLASTIC TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 3000K CCT CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4665.8 lumens
Efficiency: N/A
Efficacy: 106.0 lumens/watt
Spacing Criteria (0/90/45): 1.09 / 1.09 / 1.04
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 44
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P582583
CATALOG NUMBER: HCC6W45D010MW-HM64560830-61PSMDW

Luminous Intensity Polar Plot





TEST NUMBER: P582583

CATALOG NUMBER: HCC6W45D010MW-HM64560830-61PSMDW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20		
RC	80				70				50				30				10		0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10		0
RCR																			
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102		100
1	111	107	104	101	108	105	102	99	101	98	96	97	95	93	93	92	90		88
2	103	96	91	86	101	95	90	85	91	87	83	88	85	82	85	82	80		78
3	96	87	81	75	94	86	80	75	83	78	73	80	76	72	78	74	71		69
4	89	80	72	67	87	78	72	66	76	70	65	74	69	65	72	67	64		62
5	84	73	65	60	82	72	65	59	70	64	59	68	63	58	66	62	58		56
6	78	67	59	54	77	66	59	54	64	58	53	63	57	53	61	56	53		51
7	73	62	54	49	72	61	54	49	60	53	49	58	53	48	57	52	48		46
8	69	57	50	45	68	57	50	45	56	49	45	54	49	44	53	48	44		43
9	65	53	46	41	64	53	46	41	52	46	41	51	45	41	50	45	41		39
10	62	50	43	38	60	49	43	38	49	42	38	48	42	38	47	42	38		36

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	166768
5°	166310
10°	163836
15°	161238
20°	155933
25°	148515
30°	135603
35°	109178
40°	73588
45°	53657
50°	46378
55°	41901
60°	39756
65°	37630
70°	35407
75°	33508
80°	31222
85°	28996



TEST NUMBER: P582583

CATALOG NUMBER: HCC6W45D010MW-HM64560830-61PSMDW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	286.0	6.1
10°-20°	797.8	17.1
20°-30°	1120.9	24.0
30°-40°	997.8	21.4
40°-50°	557.6	12.0
50°-60°	397.3	8.5
60°-70°	289.1	6.2
70°-80°	167.4	3.6
80°-90°	52.0	1.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2204.7	47.3
0°-40°	3202.5	68.6
0°-60°	4157.4	89.1
0°-90°	4665.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4665.8	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3042	
5°	3022	286
15°	2841	798
25°	2455	1121
35°	1631	998
45°	692	558
55°	438	397
65°	290	289
75°	158	167
85°	46	52
90°	0	



TEST NUMBER: P582583

CATALOG NUMBER: HCC6W45D010MW-HM64560830-61PSMDW

CANDELA DISTRIBUTION (FULL):

0°	
0°	3042.1
2.5°	3028.8
5°	3022.2
7.5°	2995.8
10°	2943.2
12.5°	2893.7
15°	2841.0
17.5°	2768.5
20°	2672.9
22.5°	2567.5
25°	2455.3
27.5°	2316.9
30°	2142.2
32.5°	1918.2
35°	1631.4
37.5°	1308.5
40°	1028.3
42.5°	820.6
45°	692.1
47.5°	606.4
50°	543.8
52.5°	487.7
55°	438.4
57.5°	398.8
60°	362.6
62.5°	329.6
65°	290.1
67.5°	257.1
70°	220.9
72.5°	187.9
75°	158.2
77.5°	128.6
80°	98.9
82.5°	72.5
85°	46.1
87.5°	23.1
90°	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)