

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P582624

Luminaire Tested: **HCC6S45D010SL-HM64560840-61WDH**

Issue Date: 9/16/2021

Test Information

Test Method: LM-41-14
Report Number: P582624
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2105-241-8)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/16/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC6S45D010SL-HM64560840-61WDH
Description: HALO COMMERCIAL 6" ROUND, NEW CONSTRUCTION FRAME, WITH 6" WIDE DISTRIBUTION, HAZE TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 4000K CCT CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5302.7 lumens
Efficiency: N/A
Efficacy: 120.5 lumens/watt
Spacing Criteria (0/90/45): 1.18 / 1.18 / 1.08
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 44
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P582624
CATALOG NUMBER: HCC6S45D010SL-HM64560840-61WDH

Luminous Intensity Polar Plot





TEST NUMBER: P582624

CATALOG NUMBER: HCC6S45D010SL-HM64560840-61WDH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10		0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	113	110	107	105	110	108	105	103	103	101	100	100	98	97	96	95	94	92		
2	106	101	96	93	104	99	95	92	96	92	90	93	90	88	90	88	86	84		
3	100	93	87	83	98	91	86	82	89	84	81	86	83	80	84	81	78	77		
4	94	86	79	75	92	85	79	74	82	77	73	80	76	72	78	75	72	70		
5	89	79	73	68	87	78	72	68	76	71	67	75	70	66	73	69	66	64		
6	83	73	67	62	82	73	66	62	71	65	61	70	65	61	68	64	60	59		
7	79	68	62	57	77	68	61	57	66	60	56	65	60	56	64	59	56	54		
8	74	64	57	52	73	63	57	52	62	56	52	61	56	52	60	55	51	50		
9	70	59	53	48	69	59	53	48	58	52	48	57	52	48	56	51	48	46		
10	66	56	49	45	65	55	49	45	54	49	45	53	48	45	53	48	44	43		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	207670
5°	209057
10°	211475
15°	215813
20°	217025
25°	210266
30°	190751
35°	155088
40°	102950
45°	57293
50°	32127
55°	17825
60°	9835
65°	7446
70°	5177
75°	3791
80°	2273
85°	2264



TEST NUMBER: P582624
 CATALOG NUMBER: HCC6S45D010SL-HM64560840-61WDH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	362.6	6.8
10°-20°	1072.2	20.2
20°-30°	1580.3	29.8
30°-40°	1413.5	26.7
40°-50°	613.2	11.6
50°-60°	180.2	3.4
60°-70°	57.5	1.1
70°-80°	20.3	0.4
80°-90°	2.9	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3015.1	56.9
0°-40°	4428.6	83.5
0°-60°	5222.0	98.5
0°-90°	5302.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5302.7	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3788	
5°	3799	363
15°	3803	1072
25°	3476	1580
35°	2317	1413
45°	739	613
55°	186	180
65°	57	58
75°	18	20
85°	4	3
90°	0	



TEST NUMBER: P582624

CATALOG NUMBER: HCC6S45D010SL-HM64560840-61WDH

CANDELA DISTRIBUTION (FULL):

	0°
0°	3788.2
2.5°	3777.5
5°	3799.0
7.5°	3806.2
10°	3799.0
12.5°	3799.0
15°	3802.6
17.5°	3781.0
20°	3720.1
22.5°	3616.0
25°	3476.2
27.5°	3278.9
30°	3013.4
32.5°	2697.7
35°	2317.4
37.5°	1883.4
40°	1438.6
42.5°	1051.1
45°	739.0
47.5°	527.4
50°	376.7
52.5°	269.1
55°	186.5
57.5°	125.5
60°	89.7
62.5°	71.8
65°	57.4
67.5°	43.0
70°	32.3
72.5°	25.1
75°	17.9
77.5°	14.3
80°	7.2
82.5°	3.6
85°	3.6
87.5°	0.0
90°	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)