

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P582613

Luminaire Tested: **HCC6S45D010SL-HM64560840-61MDC**

Issue Date: 9/16/2021

**Test Information**

Test Method: LM-41-14  
Report Number: P582613  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2105-241-4)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 9/16/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: HALO COMMERCIAL  
Catalog Number: HCC6S45D010SL-HM64560840-61MDC  
Description: HALO COMMERCIAL 6" ROUND, NEW CONSTRUCTION FRAME, WITH 6" MEDIUM DISTRIBUTION, SPECULAR TRIM  
Light Source: (1) HIGH LUMEN LED 80CRI / 4000K CCT  
CYLINDER  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 5654.1 lumens  
Efficiency: N/A  
Efficacy: 128.5 lumens/watt  
Spacing Criteria (0/90/45): 1.06 / 1.06 / 0.96  
Luminous Opening: Circular (Dia: 0.5' x H: 0')  
CIE Type: Direct

Input Watts (W): 44  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P582613  
CATALOG NUMBER: HCC6S45D010SL-HM64560840-61MDC

### Luminous Intensity Polar Plot





TEST NUMBER: P582613  
 CATALOG NUMBER: HCC6S45D010SL-HM64560840-61MDC

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	114	111	108	106	111	109	106	104	105	103	101	101	99	98	97	96	95	94
2	108	103	99	96	106	101	98	95	98	95	93	95	93	91	92	90	89	87
3	102	96	91	87	100	95	90	86	92	88	85	90	86	84	87	85	82	81
4	97	90	84	80	95	89	83	79	86	82	79	84	81	78	83	79	77	75
5	92	84	78	74	91	83	78	73	81	76	73	80	75	72	78	74	72	70
6	88	79	73	68	86	78	72	68	76	71	68	75	71	67	74	70	67	65
7	83	74	68	64	82	73	68	63	72	67	63	71	66	63	70	66	62	61
8	79	70	63	59	78	69	63	59	68	63	59	67	62	59	66	62	58	57
9	75	66	60	56	74	65	59	55	64	59	55	63	58	55	62	58	55	54
10	72	62	56	52	71	61	56	52	61	55	52	60	55	52	59	55	52	50

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	268493
5°	272677
10°	288210
15°	320904
20°	332791
25°	273052
30°	191333
35°	130533
40°	67992
45°	23909
50°	10703
55°	3431
60°	1963
65°	1401
70°	1154
75°	763
80°	0
85°	0



TEST NUMBER: P582613  
 CATALOG NUMBER: HCC6S45D010SL-HM64560840-61MDC

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	480.0	8.5
10°-20°	1590.2	28.1
20°-30°	2024.8	35.8
30°-40°	1206.7	21.3
40°-50°	292.6	5.2
50°-60°	44.9	0.8
60°-70°	11.1	0.2
70°-80°	3.8	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	4095.0	72.4
0°-40°	5301.7	93.8
0°-60°	5639.3	99.7
0°-90°	5654.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5654.1	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	4898	
5°	4955	480
15°	5654	1590
25°	4514	2025
35°	1950	1207
45°	308	293
55°	36	45
65°	11	11
75°	4	4
85°	0	0
90°	0	



TEST NUMBER: P582613  
CATALOG NUMBER: HCC6S45D010SL-HM64560840-61MDC

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	4897.7
2.5°	4897.7
5°	4955.1
7.5°	5044.8
10°	5177.5
12.5°	5385.5
15°	5654.3
17.5°	5822.9
20°	5704.5
22.5°	5249.2
25°	4514.2
27.5°	3703.9
30°	3022.6
32.5°	2470.5
35°	1950.5
37.5°	1437.7
40°	950.1
42.5°	512.7
45°	308.4
47.5°	193.7
50°	125.5
52.5°	75.3
55°	35.9
57.5°	21.5
60°	17.9
62.5°	14.3
65°	10.8
67.5°	7.2
70°	7.2
72.5°	3.6
75°	3.6
77.5°	3.6
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)