

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P593318

Luminaire Tested: **HCC6S45D010SL-HM64560850-61WDW**

Issue Date: 9/16/2021

Test Information

Test Method: LM-41-14
Report Number: P593318
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2105-241-9)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/16/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC6S45D010SL-HM64560850-61WDW
Description: HALO COMMERCIAL 6" ROUND, NEW CONSTRUCTION FRAME, WITH 6" WIDE DISTRIBUTION, WHITE TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 5000K CCT CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5234.6 lumens
Efficiency: N/A
Efficacy: 119.0 lumens/watt
Spacing Criteria (0/90/45): 1.11 / 1.11 / 1.09
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 44
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P593318
CATALOG NUMBER: HCC6S45D010SL-HM64560850-61WDW

Luminous Intensity Polar Plot





TEST NUMBER: P593318

CATALOG NUMBER: HCC6S45D010SL-HM64560850-61WDW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	111	107	104	101	108	105	102	99	101	98	96	97	95	93	94	92	90	89			
2	103	97	91	87	101	95	90	86	91	87	84	88	85	82	85	83	80	78			
3	96	87	81	76	94	86	80	75	83	78	74	81	76	72	78	74	71	69			
4	89	80	72	67	87	78	72	66	76	70	66	74	69	65	72	67	64	62			
5	84	73	65	60	82	72	65	59	70	64	59	68	63	58	66	61	58	56			
6	78	67	59	54	76	66	59	54	64	58	53	63	57	53	61	56	52	51			
7	73	62	54	49	72	61	54	49	60	53	48	58	52	48	57	52	48	46			
8	69	57	50	45	68	57	50	45	55	49	44	54	48	44	53	48	44	42			
9	65	53	46	41	64	53	46	41	52	45	41	51	45	41	50	44	41	39			
10	61	50	43	38	60	49	42	38	48	42	38	47	42	38	47	41	38	36			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	178632
5°	178527
10°	176795
15°	174967
20°	170016
25°	162844
30°	151125
35°	130032
40°	94914
45°	65030
50°	52280
55°	45561
60°	42058
65°	39991
70°	37346
75°	34927
80°	31696
85°	27047



TEST NUMBER: P593318
 CATALOG NUMBER: HCC6S45D010SL-HM64560850-61WDW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	307.5	5.9
10°-20°	865.8	16.5
20°-30°	1231.4	23.5
30°-40°	1185.5	22.6
40°-50°	682.1	13.0
50°-60°	432.2	8.3
60°-70°	306.0	5.8
70°-80°	174.4	3.3
80°-90°	49.7	0.9
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2404.7	45.9
0°-40°	3590.2	68.6
0°-60°	4704.5	89.9
0°-90°	5234.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5234.6	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3258	
5°	3244	308
15°	3083	866
25°	2692	1231
35°	1943	1186
45°	839	682
55°	477	432
65°	308	306
75°	165	174
85°	43	50
90°	0	



TEST NUMBER: P593318
CATALOG NUMBER: HCC6S45D010SL-HM64560850-61WDW

CANDELA DISTRIBUTION (FULL):

	0°
0°	3258.5
2.5°	3244.2
5°	3244.2
7.5°	3222.6
10°	3176.0
12.5°	3129.4
15°	3082.9
17.5°	3011.1
20°	2914.3
22.5°	2806.8
25°	2692.2
27.5°	2552.3
30°	2387.4
32.5°	2186.7
35°	1943.0
37.5°	1645.4
40°	1326.3
42.5°	1046.8
45°	838.8
47.5°	706.1
50°	613.0
52.5°	537.7
55°	476.7
57.5°	423.0
60°	383.6
62.5°	347.7
65°	308.3
67.5°	272.5
70°	233.0
72.5°	197.2
75°	164.9
77.5°	132.7
80°	100.4
82.5°	71.7
85°	43.0
87.5°	17.9
90°	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)