

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P582631

Luminaire Tested: **HCC6S45D010BZ-HM64560927-61MDC**

Issue Date: 9/16/2021

Test Information

Test Method: LM-41-14
Report Number: P582631
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2105-241-4)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/16/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC6S45D010BZ-HM64560927-61MDC
Description: HALO COMMERCIAL 6" ROUND, NEW CONSTRUCTION FRAME, WITH 6" MEDIUM DISTRIBUTION, SPECULAR TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4001.0 lumens
Efficiency: N/A
Efficacy: 90.9 lumens/watt
Spacing Criteria (0/90/45): 1.06 / 1.06 / 0.96
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 44
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P582631
CATALOG NUMBER: HCC6S45D010BZ-HM64560927-61MDC

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P582631

CATALOG NUMBER: HCC6S45D010BZ-HM64560927-61MDC

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	114	111	108	106	111	109	106	104	105	103	101	101	99	98	97	96	95	94			
2	108	103	99	96	106	101	98	95	98	95	93	95	93	91	92	90	89	87			
3	102	96	91	87	100	95	90	86	92	88	85	90	86	84	87	85	82	81			
4	97	90	84	80	95	89	83	79	86	82	79	84	81	78	83	79	77	75			
5	92	84	78	74	91	83	78	73	81	76	73	80	75	72	78	74	72	70			
6	88	79	73	68	86	78	72	68	76	71	68	75	71	67	74	70	67	65			
7	83	74	68	64	82	73	68	63	72	67	63	71	66	63	70	66	62	61			
8	79	70	63	59	78	69	63	59	68	63	59	67	62	59	66	62	58	57			
9	75	66	60	56	74	65	59	55	64	59	55	63	58	55	62	58	55	54			
10	72	62	56	52	71	61	56	52	61	55	52	60	55	52	59	55	52	50			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	189990
5°	192950
10°	203937
15°	227078
20°	235489
25°	193215
30°	135388
35°	92374
40°	48119
45°	16916
50°	7573
55°	2418
60°	1392
65°	986
70°	801
75°	551
80°	0
85°	0



TEST NUMBER: P582631
 CATALOG NUMBER: HCC6S45D010BZ-HM64560927-61MDC

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	339.6	8.5
10°-20°	1125.3	28.1
20°-30°	1432.8	35.8
30°-40°	853.9	21.3
40°-50°	207.1	5.2
50°-60°	31.8	0.8
60°-70°	7.8	0.2
70°-80°	2.7	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2897.7	72.4
0°-40°	3751.6	93.8
0°-60°	3990.4	99.7
0°-90°	4001.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4001.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3466	
5°	3506	340
15°	4001	1125
25°	3194	1433
35°	1380	854
45°	218	207
55°	25	32
65°	8	8
75°	3	3
85°	0	0
90°	0	



TEST NUMBER: P582631
CATALOG NUMBER: HCC6S45D010BZ-HM64560927-61MDC

CANDELA DISTRIBUTION (FULL):

	0°
0°	3465.7
2.5°	3465.7
5°	3506.3
7.5°	3569.8
10°	3663.6
12.5°	3810.8
15°	4001.1
17.5°	4120.4
20°	4036.6
22.5°	3714.4
25°	3194.3
27.5°	2621.0
30°	2138.8
32.5°	1748.1
35°	1380.3
37.5°	1017.5
40°	672.4
42.5°	362.8
45°	218.2
47.5°	137.0
50°	88.8
52.5°	53.3
55°	25.3
57.5°	15.2
60°	12.7
62.5°	10.2
65°	7.6
67.5°	5.0
70°	5.0
72.5°	2.6
75°	2.6
77.5°	2.6
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)