

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P582636

Luminaire Tested: **HCC6W45D010MB-HM64560927-61NDW**

Issue Date: 9/16/2021

Test Information

Test Method: LM-41-14
Report Number: P582636
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2105-241-3)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/16/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC6W45D010MB-HM64560927-61NDW
Description: HALO COMMERCIAL 6" ROUND, NEW CONSTRUCTION FRAME, WITH 6" NARROW DISTRIBUTION, WHITE TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3453.0 lumens
Efficiency: N/A
Efficacy: 78.5 lumens/watt
Spacing Criteria (0/90/45): 1.06 / 1.06 / 1.03
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 44
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P582636
CATALOG NUMBER: HCC6W45D010MB-HM64560927-61NDW

Luminous Intensity Polar Plot





TEST NUMBER: P582636

CATALOG NUMBER: HCC6W45D010MB-HM64560927-61NDW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	111	108	104	101	109	105	102	100	101	99	96	97	95	94	94	92	91	89			89
2	104	97	92	87	101	95	90	86	92	88	84	89	85	83	86	83	81	79			79
3	97	88	82	77	94	87	81	76	84	79	75	81	77	73	79	75	72	70			70
4	90	81	73	68	88	79	73	68	77	71	67	75	70	66	73	69	65	63			63
5	84	74	67	61	83	73	66	61	71	65	60	69	64	60	67	63	59	57			57
6	79	68	61	55	77	67	60	55	66	59	55	64	59	54	63	58	54	52			52
7	74	63	56	50	73	62	55	50	61	55	50	60	54	50	58	53	49	48			48
8	70	59	51	46	69	58	51	46	57	50	46	56	50	46	54	49	46	44			44
9	66	55	48	43	65	54	47	43	53	47	42	52	46	42	51	46	42	41			41
10	62	51	44	40	61	51	44	40	50	44	39	49	43	39	48	43	39	38			38

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	130779
5°	130167
10°	127286
15°	124303
20°	119629
25°	113142
30°	102820
35°	83226
40°	56127
45°	38570
50°	31607
55°	27660
60°	26160
65°	24698
70°	23177
75°	22028
80°	20047
85°	17549



TEST NUMBER: P582636
 CATALOG NUMBER: HCC6W45D010MB-HM64560927-61NDW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	223.3	6.5
10°-20°	615.1	17.8
20°-30°	854.5	24.7
30°-40°	760.8	22.0
40°-50°	403.9	11.7
50°-60°	264.2	7.7
60°-70°	189.3	5.5
70°-80°	109.7	3.2
80°-90°	32.1	0.9
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1692.9	49.0
0°-40°	2453.8	71.1
0°-60°	3121.8	90.4
0°-90°	3453.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3453.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2386	
5°	2365	223
15°	2190	615
25°	1870	855
35°	1244	761
45°	498	404
55°	289	264
65°	190	189
75°	104	110
85°	28	32
90°	0	



TEST NUMBER: P582636
CATALOG NUMBER: HCC6W45D010MB-HM64560927-61NDW

CANDELA DISTRIBUTION (FULL):

0°	
0°	2385.6
2.5°	2373.0
5°	2365.4
7.5°	2337.4
10°	2286.6
12.5°	2241.0
15°	2190.2
17.5°	2126.8
20°	2050.6
22.5°	1964.4
25°	1870.5
27.5°	1761.4
30°	1624.3
32.5°	1459.3
35°	1243.6
37.5°	1005.0
40°	784.3
42.5°	609.1
45°	497.5
47.5°	423.8
50°	370.6
52.5°	327.4
55°	289.4
57.5°	261.5
60°	238.6
62.5°	215.7
65°	190.4
67.5°	167.5
70°	144.6
72.5°	124.3
75°	104.0
77.5°	83.8
80°	63.5
82.5°	45.6
85°	27.9
87.5°	12.7
90°	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)