

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P582658

Luminaire Tested: **HCC6W45D010SL-HM64560930-61WDBB**

Issue Date: 9/16/2021

Test Information

Test Method: LM-41-14
Report Number: P582658
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2105-241-11)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/16/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC6W45D010SL-HM64560930-61WDBB
Description: HALO COMMERCIAL 6" ROUND, NEW CONSTRUCTION FRAME, WITH 6" WIDE DISTRIBUTION, BLACK BAFFLE TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4000.9 lumens
Efficiency: N/A
Efficacy: 90.9 lumens/watt
Spacing Criteria (0/90/45): 1.32 / 1.32 / 1.14
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 44
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P582658
CATALOG NUMBER: HCC6W45D010SL-HM64560930-61WDBB

Luminous Intensity Polar Plot





TEST NUMBER: P582658
 CATALOG NUMBER: HCC6W45D010SL-HM64560930-61WDBB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	113	110	107	105	110	108	105	103	104	102	100	100	98	97	97	95	94				92
2	107	101	97	93	104	100	95	92	96	93	90	93	91	88	90	88	86				85
3	100	93	88	83	98	92	87	83	89	85	81	87	83	80	84	81	79				77
4	95	86	80	75	93	85	79	75	83	78	74	81	77	73	79	75	72				71
5	89	80	73	68	87	79	73	68	77	72	67	75	70	67	73	69	66				65
6	84	74	67	62	82	73	67	62	71	66	62	70	65	61	69	64	61				59
7	79	68	62	57	77	68	61	57	66	61	57	65	60	56	64	59	56				54
8	74	64	57	52	73	63	57	52	62	56	52	61	56	52	60	55	52				50
9	70	59	53	48	69	59	53	48	58	52	48	57	52	48	56	51	48				46
10	66	56	49	45	65	55	49	45	54	48	45	53	48	44	53	48	44				43

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	142094
5°	143132
10°	145627
15°	151408
20°	157753
25°	163382
30°	161196
35°	134308
40°	86126
45°	43004
50°	17066
55°	5792
60°	1656
65°	1180
70°	978
75°	1292
80°	947
85°	0



TEST NUMBER: P582658
 CATALOG NUMBER: HCC6W45D010SL-HM64560930-61WDBB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	248.7	6.2
10°-20°	756.6	18.9
20°-30°	1235.5	30.9
30°-40°	1211.1	30.3
40°-50°	464.4	11.6
50°-60°	68.1	1.7
60°-70°	10.1	0.3
70°-80°	5.2	0.1
80°-90°	1.2	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2240.8	56.0
0°-40°	3451.9	86.3
0°-60°	3984.4	99.6
0°-90°	4000.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4000.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2592	
5°	2601	249
15°	2668	757
25°	2701	1235
35°	2007	1211
45°	555	464
55°	61	68
65°	9	10
75°	6	5
85°	0	1
90°	0	



TEST NUMBER: P582658
CATALOG NUMBER: HCC6W45D010SL-HM64560930-61WDBB

CANDELA DISTRIBUTION (FULL):

	0°
0°	2592.0
2.5°	2585.9
5°	2601.0
7.5°	2610.2
10°	2616.1
12.5°	2637.4
15°	2667.8
17.5°	2691.9
20°	2704.1
22.5°	2707.2
25°	2701.1
27.5°	2658.6
30°	2546.5
32.5°	2334.3
35°	2006.9
37.5°	1603.6
40°	1203.5
42.5°	857.9
45°	554.7
47.5°	339.6
50°	200.1
52.5°	115.2
55°	60.6
57.5°	27.3
60°	15.1
62.5°	12.1
65°	9.1
67.5°	9.1
70°	6.1
72.5°	6.1
75°	6.1
77.5°	3.0
80°	3.0
82.5°	3.0
85°	0.0
87.5°	0.0
90°	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)