

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P582672

Luminaire Tested: **HCC6S45D010MW-HM64560935-61NDW**

Issue Date: 9/16/2021

Test Information

Test Method: LM-41-14
Report Number: P582672
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2105-241-3)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/16/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC6S45D010MW-HM64560935-61NDW
Description: HALO COMMERCIAL 6" ROUND, NEW CONSTRUCTION FRAME, WITH 6" NARROW DISTRIBUTION, WHITE TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT
CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4173.7 lumens
Efficiency: N/A
Efficacy: 94.9 lumens/watt
Spacing Criteria (0/90/45): 1.06 / 1.06 / 1.03
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 44
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P582672
CATALOG NUMBER: HCC6S45D010MW-HM64560935-61NDW

Luminous Intensity Polar Plot





TEST NUMBER: P582672
 CATALOG NUMBER: HCC6S45D010MW-HM64560935-61NDW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	111	108	104	101	109	105	102	100	101	99	96	97	95	94	94	92	91	89
2	104	97	92	87	101	95	90	86	92	88	84	89	85	83	86	83	81	79
3	97	88	82	77	94	87	81	76	84	79	75	81	77	73	79	75	72	70
4	90	81	73	68	88	79	73	68	77	71	67	75	70	66	73	69	65	63
5	84	74	67	61	83	73	66	61	71	65	60	69	64	60	67	63	59	57
6	79	68	61	55	77	67	60	55	66	59	55	64	59	54	63	58	54	52
7	74	63	56	50	73	62	55	50	61	55	50	60	54	50	58	53	49	48
8	70	59	51	46	69	58	51	46	57	50	46	56	50	46	54	49	46	44
9	66	55	48	43	65	54	47	43	53	47	42	52	46	42	51	46	42	41
10	62	51	44	40	61	51	44	40	50	44	39	49	43	39	48	43	39	38

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	158079
5°	157335
10°	153855
15°	150256
20°	144603
25°	136750
30°	124285
35°	100599
40°	67834
45°	46617
50°	38199
55°	33423
60°	31609
65°	29835
70°	28034
75°	26624
80°	24214
85°	21260



TEST NUMBER: P582672
 CATALOG NUMBER: HCC6S45D010MW-HM64560935-61NDW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	269.9	6.5
10°-20°	743.5	17.8
20°-30°	1032.9	24.7
30°-40°	919.7	22.0
40°-50°	488.2	11.7
50°-60°	319.3	7.6
60°-70°	228.8	5.5
70°-80°	132.7	3.2
80°-90°	38.8	0.9
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2046.3	49.0
0°-40°	2965.9	71.1
0°-60°	3773.4	90.4
0°-90°	4173.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4173.7	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2884	
5°	2859	270
15°	2648	743
25°	2261	1033
35°	1503	920
45°	601	488
55°	350	319
65°	230	229
75°	126	133
85°	34	39
90°	0	



TEST NUMBER: P582672
CATALOG NUMBER: HCC6S45D010MW-HM64560935-61NDW

CANDELA DISTRIBUTION (FULL):

	0°
0°	2883.6
2.5°	2868.3
5°	2859.1
7.5°	2825.3
10°	2763.9
12.5°	2708.8
15°	2647.5
17.5°	2570.7
20°	2478.7
22.5°	2374.4
25°	2260.8
27.5°	2129.0
30°	1963.4
32.5°	1764.0
35°	1503.2
37.5°	1214.8
40°	947.9
42.5°	736.3
45°	601.3
47.5°	512.2
50°	447.9
52.5°	395.8
55°	349.7
57.5°	316.0
60°	288.3
62.5°	260.8
65°	230.0
67.5°	202.5
70°	174.9
72.5°	150.3
75°	125.7
77.5°	101.2
80°	76.7
82.5°	55.2
85°	33.8
87.5°	15.4
90°	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)