

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P582669

Luminaire Tested: **HCC6W45D010BZ-HM64560935-61MDW**

Issue Date: 9/16/2021

Test Information

Test Method: LM-41-14
Report Number: P582669
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2105-241-6)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/16/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC6W45D010BZ-HM64560935-61MDW
Description: HALO COMMERCIAL 6" ROUND, NEW CONSTRUCTION FRAME, WITH 6" MEDIUM DISTRIBUTION, WHITE TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4235.0 lumens
Efficiency: N/A
Efficacy: 96.2 lumens/watt
Spacing Criteria (0/90/45): 1.08 / 1.08 / 1.03
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 44
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P582669
CATALOG NUMBER: HCC6W45D010BZ-HM64560935-61MDW

Luminous Intensity Polar Plot





TEST NUMBER: P582669

CATALOG NUMBER: HCC6W45D010BZ-HM64560935-61MDW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	111	108	104	101	109	105	102	100	101	99	96	97	95	94	94	92	91	89			89
2	104	97	92	87	101	95	90	86	92	88	84	89	85	82	86	83	81	79			79
3	97	88	82	76	94	87	81	76	84	79	75	81	77	73	79	75	72	70			70
4	90	80	73	68	88	79	73	67	77	71	67	75	70	66	73	68	65	63			63
5	84	74	66	61	82	73	66	61	71	65	60	69	64	59	67	63	59	57			57
6	79	68	61	55	77	67	60	55	65	59	55	64	58	54	62	58	54	52			52
7	74	63	55	50	73	62	55	50	61	54	50	59	54	50	58	53	49	48			48
8	70	58	51	46	69	58	51	46	57	50	46	55	50	46	54	49	45	44			44
9	66	54	47	43	65	54	47	42	53	47	42	52	46	42	51	46	42	40			40
10	62	51	44	39	61	50	44	39	49	43	39	49	43	39	48	43	39	37			37

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	157652
5°	157076
10°	154450
15°	151732
20°	146482
25°	138903
30°	126342
35°	100947
40°	67355
45°	48013
50°	40007
55°	34866
60°	32936
65°	31028
70°	28498
75°	26624
80°	24182
85°	21260



TEST NUMBER: P582669
 CATALOG NUMBER: HCC6W45D010BZ-HM64560935-61MDW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	270.0	6.4
10°-20°	750.7	17.7
20°-30°	1049.0	24.8
30°-40°	924.0	21.8
40°-50°	499.2	11.8
50°-60°	333.8	7.9
60°-70°	236.6	5.6
70°-80°	133.0	3.1
80°-90°	38.8	0.9
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2069.6	48.9
0°-40°	2993.6	70.7
0°-60°	3826.6	90.4
0°-90°	4235.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4235.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2876	
5°	2854	270
15°	2674	751
25°	2296	1049
35°	1508	924
45°	619	499
55°	365	334
65°	239	237
75°	126	133
85°	34	39
90°	0	



TEST NUMBER: P582669
CATALOG NUMBER: HCC6W45D010BZ-HM64560935-61MDW

CANDELA DISTRIBUTION (FULL):

	0°
0°	2875.8
2.5°	2860.5
5°	2854.4
7.5°	2826.7
10°	2774.6
12.5°	2725.6
15°	2673.5
17.5°	2602.9
20°	2510.9
22.5°	2409.8
25°	2296.4
27.5°	2164.5
30°	1995.9
32.5°	1787.4
35°	1508.4
37.5°	1204.9
40°	941.2
42.5°	741.9
45°	619.3
47.5°	536.5
50°	469.1
52.5°	414.0
55°	364.8
57.5°	331.1
60°	300.4
62.5°	269.8
65°	239.2
67.5°	208.4
70°	177.8
72.5°	150.3
75°	125.7
77.5°	101.2
80°	76.6
82.5°	55.1
85°	33.8
87.5°	15.4
90°	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)