

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P582696

Luminaire Tested: **HCC6W45D010MB-HM64560940-61WDH**

Issue Date: 9/16/2021

Test Information

Test Method: LM-41-14
Report Number: P582696
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2105-241-8)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/16/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC6W45D010MB-HM64560940-61WDH
Description: HALO COMMERCIAL 6" ROUND, NEW CONSTRUCTION FRAME, WITH 6" WIDE DISTRIBUTION, HAZE TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 4000K CCT CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4678.7 lumens
Efficiency: N/A
Efficacy: 106.3 lumens/watt
Spacing Criteria (0/90/45): 1.18 / 1.18 / 1.08
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 44
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P582696
CATALOG NUMBER: HCC6W45D010MB-HM64560940-61WDH

Luminous Intensity Polar Plot





TEST NUMBER: P582696

CATALOG NUMBER: HCC6W45D010MB-HM64560940-61WDH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	113	110	107	105	110	108	105	103	103	101	100	100	98	97	96	95	94	92	92	92	92
2	106	101	96	93	104	99	95	92	96	92	90	93	90	88	90	88	86	84	84	84	84
3	100	93	87	83	98	91	86	82	89	84	81	86	83	80	84	81	78	77	77	77	77
4	94	86	79	75	92	85	79	74	82	77	73	80	76	72	78	75	72	70	70	70	70
5	89	79	73	68	87	78	72	68	76	71	67	75	70	66	73	69	66	64	64	64	64
6	83	73	67	62	82	73	66	62	71	65	61	70	65	61	68	64	60	59	59	59	59
7	79	68	62	57	77	68	61	57	66	60	56	65	60	56	64	59	56	54	54	54	54
8	74	64	57	52	73	63	57	52	62	56	52	61	56	52	60	55	51	50	50	50	50
9	70	59	53	48	69	59	53	48	58	52	48	57	52	48	56	51	48	46	46	46	46
10	66	56	49	45	65	55	49	45	54	49	45	53	48	45	53	48	44	43	43	43	43

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	183236
5°	184459
10°	186592
15°	190415
20°	191484
25°	185515
30°	168298
35°	136838
40°	90827
45°	50556
50°	28340
55°	15732
60°	8684
65°	6577
70°	4568
75°	3347
80°	1989
85°	2013



TEST NUMBER: P582696
 CATALOG NUMBER: HCC6W45D010MB-HM64560940-61WDH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	319.9	6.8
10°-20°	946.0	20.2
20°-30°	1394.3	29.8
30°-40°	1247.1	26.7
40°-50°	541.1	11.6
50°-60°	159.0	3.4
60°-70°	50.8	1.1
70°-80°	17.9	0.4
80°-90°	2.6	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2660.3	56.9
0°-40°	3907.4	83.5
0°-60°	4607.4	98.5
0°-90°	4678.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4678.7	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3342	
5°	3352	320
15°	3355	946
25°	3067	1394
35°	2045	1247
45°	652	541
55°	165	159
65°	51	51
75°	16	18
85°	3	3
90°	0	



TEST NUMBER: P582696

CATALOG NUMBER: HCC6W45D010MB-HM64560940-61WDH

CANDELA DISTRIBUTION (FULL):

	0°
0°	3342.5
2.5°	3333.0
5°	3352.0
7.5°	3358.3
10°	3352.0
12.5°	3352.0
15°	3355.1
17.5°	3336.1
20°	3282.3
22.5°	3190.6
25°	3067.0
27.5°	2893.0
30°	2658.7
32.5°	2380.3
35°	2044.7
37.5°	1661.7
40°	1269.2
42.5°	927.4
45°	652.1
47.5°	465.3
50°	332.3
52.5°	237.4
55°	164.6
57.5°	110.7
60°	79.2
62.5°	63.3
65°	50.7
67.5°	38.0
70°	28.5
72.5°	22.2
75°	15.8
77.5°	12.7
80°	6.3
82.5°	3.2
85°	3.2
87.5°	0.0
90°	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)