

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P582688

Luminaire Tested: **HCC6S45D010SL-HM64560940-61NDC**

Issue Date: 9/16/2021

Test Information

Test Method: LM-41-14
Report Number: P582688
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2105-241-1)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/16/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC6S45D010SL-HM64560940-61NDC
Description: HALO COMMERCIAL 6" ROUND, NEW CONSTRUCTION FRAME, WITH 6" NARROW DISTRIBUTION, SPECULAR TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 4000K CCT CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4817.9 lumens
Efficiency: N/A
Efficacy: 109.5 lumens/watt
Spacing Criteria (0/90/45): 0.93 / 0.93 / 0.88
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 44
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P582688
CATALOG NUMBER: HCC6S45D010SL-HM64560940-61NDC

Luminous Intensity Polar Plot





TEST NUMBER: P582688

CATALOG NUMBER: HCC6S45D010SL-HM64560940-61NDC

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	114	111	108	106	111	109	107	105	105	103	101	101	100	98	98	97	96	94	94	94	94
2	108	103	99	96	106	102	98	95	98	96	93	96	93	91	93	91	89	87	87	87	87
3	103	97	92	88	101	95	91	87	93	89	86	90	87	84	88	85	83	82	82	82	82
4	98	90	85	81	96	89	84	80	87	83	79	85	81	79	83	80	78	76	76	76	76
5	93	85	79	75	91	84	79	75	82	77	74	80	76	73	79	75	73	71	71	71	71
6	88	80	74	70	87	79	73	69	77	73	69	76	72	68	75	71	68	67	67	67	67
7	84	75	69	65	83	74	69	65	73	68	64	72	67	64	71	67	64	62	62	62	62
8	80	71	65	61	79	70	65	61	69	64	60	68	64	60	67	63	60	59	59	59	59
9	76	67	61	57	75	66	61	57	65	60	57	65	60	57	64	60	56	55	55	55	55
10	73	63	58	54	72	63	57	54	62	57	54	61	57	53	61	56	53	52	52	52	52

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	287724
5°	288305
10°	293042
15°	295183
20°	269833
25°	212032
30°	155201
35°	110095
40°	52069
45°	19870
50°	8904
55°	2418
60°	1042
65°	817
70°	513
75°	678
80°	0
85°	0



TEST NUMBER: P582688
 CATALOG NUMBER: HCC6S45D010SL-HM64560940-61NDC

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	501.2	10.4
10°-20°	1437.5	29.8
20°-30°	1599.0	33.2
30°-40°	998.9	20.7
40°-50°	237.3	4.9
50°-60°	34.0	0.7
60°-70°	7.0	0.1
70°-80°	3.0	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3537.7	73.4
0°-40°	4536.6	94.2
0°-60°	4807.9	99.8
0°-90°	4817.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4817.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	5248	
5°	5239	501
15°	5201	1438
25°	3505	1599
35°	1645	999
45°	256	237
55°	25	34
65°	6	7
75°	3	3
85°	0	0
90°	0	



TEST NUMBER: P582688
CATALOG NUMBER: HCC6S45D010SL-HM64560940-61NDC

CANDELA DISTRIBUTION (FULL):

	0°
0°	5248.5
2.5°	5226.4
5°	5239.1
7.5°	5258.0
10°	5264.3
12.5°	5261.1
15°	5201.1
17.5°	4998.6
20°	4625.3
22.5°	4100.1
25°	3505.4
27.5°	2935.9
30°	2451.8
32.5°	2050.1
35°	1645.1
37.5°	1208.5
40°	727.6
42.5°	420.8
45°	256.3
47.5°	164.5
50°	104.4
52.5°	60.1
55°	25.3
57.5°	12.7
60°	9.5
62.5°	9.5
65°	6.3
67.5°	6.3
70°	3.2
72.5°	3.2
75°	3.2
77.5°	3.2
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)