

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P593333

Luminaire Tested: **HCC6S45D010MB-HM64560950-61PSMDW**

Issue Date: 9/16/2021

Test Information

Test Method: LM-41-14
Report Number: P593333
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2105-241-12)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/16/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC6S45D010MB-HM64560950-61PSMDW
Description: HALO COMMERCIAL 6" ROUND, NEW CONSTRUCTION FRAME, WITH 6" PLASTIC TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 5000K CCT
CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4479.4 lumens
Efficiency: N/A
Efficacy: 101.8 lumens/watt
Spacing Criteria (0/90/45): 1.09 / 1.09 / 1.04
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 44
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P593333
CATALOG NUMBER: HCC6S45D010MB-HM64560950-61PSMDW

Luminous Intensity Polar Plot





TEST NUMBER: P593333
 CATALOG NUMBER: HCC6S45D010MB-HM64560950-61PSMDW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20		
RC	80				70				50				30				10		0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10		0
RCR																			
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102		100
1	111	107	104	101	108	105	102	99	101	98	96	97	95	93	93	92	90		88
2	103	96	91	86	101	95	90	85	91	87	83	88	85	82	85	82	80		78
3	96	87	81	75	94	86	80	75	83	78	73	80	76	72	78	74	71		69
4	89	80	72	67	87	78	72	66	76	70	65	74	69	65	72	67	64		62
5	84	73	65	60	82	72	65	59	70	64	59	68	63	58	66	62	58		56
6	78	67	59	54	77	66	59	54	64	58	53	63	57	53	61	56	53		51
7	73	62	54	49	72	61	54	49	60	53	49	58	53	48	57	52	48		46
8	69	57	50	45	68	57	50	45	56	49	45	54	49	44	53	48	44		43
9	65	53	46	41	64	53	46	41	52	46	41	51	45	41	50	45	41		39
10	62	50	43	38	60	49	43	38	49	42	38	48	42	38	47	42	38		36

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	160102
5°	159668
10°	157284
15°	154797
20°	149708
25°	142587
30°	130191
35°	104822
40°	70647
45°	51517
50°	44527
55°	40228
60°	38155
65°	36126
70°	33980
75°	32174
80°	29960
85°	27864



TEST NUMBER: P593333
 CATALOG NUMBER: HCC6S45D010MB-HM64560950-61PSMDW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	274.6	6.1
10°-20°	765.9	17.1
20°-30°	1076.1	24.0
30°-40°	957.9	21.4
40°-50°	535.3	12.0
50°-60°	381.4	8.5
60°-70°	277.5	6.2
70°-80°	160.7	3.6
80°-90°	49.9	1.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2116.7	47.3
0°-40°	3074.6	68.6
0°-60°	3991.3	89.1
0°-90°	4479.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4479.4	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2920	
5°	2902	275
15°	2728	766
25°	2357	1076
35°	1566	958
45°	664	535
55°	421	381
65°	278	277
75°	152	161
85°	44	50
90°	0	



TEST NUMBER: P593333
CATALOG NUMBER: HCC6S45D010MB-HM64560950-61PSMDW

CANDELA DISTRIBUTION (FULL):

	0°
0°	2920.5
2.5°	2907.9
5°	2901.5
7.5°	2876.2
10°	2825.5
12.5°	2778.1
15°	2727.5
17.5°	2657.9
20°	2566.2
22.5°	2464.8
25°	2357.3
27.5°	2224.4
30°	2056.7
32.5°	1841.5
35°	1566.3
37.5°	1256.2
40°	987.2
42.5°	787.9
45°	664.5
47.5°	582.2
50°	522.1
52.5°	468.3
55°	420.9
57.5°	382.9
60°	348.0
62.5°	316.4
65°	278.5
67.5°	246.8
70°	212.0
72.5°	180.4
75°	151.9
77.5°	123.4
80°	94.9
82.5°	69.6
85°	44.3
87.5°	22.2
90°	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)