

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P582708

Luminaire Tested: **HCC6W50D010BZ-HM64560827-61NDW**

Issue Date: 9/16/2021

Test Information

Test Method: LM-41-14
Report Number: P582708
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2105-241-3)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/16/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC6W50D010BZ-HM64560827-61NDW
Description: HALO COMMERCIAL 6" ROUND, NEW CONSTRUCTION FRAME, WITH 6" NARROW DISTRIBUTION, WHITE TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 2700K CCT CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4394.7 lumens
Efficiency: N/A
Efficacy: 91.6 lumens/watt
Spacing Criteria (0/90/45): 1.06 / 1.06 / 1.03
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 48
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P582708
CATALOG NUMBER: HCC6W50D010BZ-HM64560827-61NDW

Luminous Intensity Polar Plot





TEST NUMBER: P582708
 CATALOG NUMBER: HCC6W50D010BZ-HM64560827-61NDW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10		0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	111	108	104	101	109	105	102	100	101	99	96	97	95	94	94	92	91	89		
2	104	97	92	87	101	95	90	86	92	88	84	89	85	83	86	83	81	79		
3	97	88	82	77	94	87	81	76	84	79	75	81	77	73	79	75	72	70		
4	90	81	73	68	88	79	73	68	77	71	67	75	70	66	73	69	65	63		
5	84	74	67	61	83	73	66	61	71	65	60	69	64	60	67	63	59	57		
6	79	68	61	55	77	67	60	55	66	59	55	64	59	54	63	58	54	52		
7	74	63	56	50	73	62	55	50	61	55	50	60	54	50	58	53	49	48		
8	70	59	51	46	69	58	51	46	57	50	46	56	50	46	54	49	46	44		
9	66	55	48	43	65	54	47	43	53	47	42	52	46	42	51	46	42	41		
10	62	51	44	40	61	51	44	40	50	44	39	49	43	39	48	43	39	38		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	166456
5°	165667
10°	162004
15°	158207
20°	152263
25°	144002
30°	130862
35°	105926
40°	71434
45°	49083
50°	40220
55°	35191
60°	33287
65°	31417
70°	29508
75°	28043
80°	25508
85°	22329



TEST NUMBER: P582708
 CATALOG NUMBER: HCC6W50D010BZ-HM64560827-61NDW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	284.2	6.5
10°-20°	782.8	17.8
20°-30°	1087.6	24.7
30°-40°	968.4	22.0
40°-50°	514.1	11.7
50°-60°	336.2	7.6
60°-70°	240.9	5.5
70°-80°	139.7	3.2
80°-90°	40.9	0.9
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2154.7	49.0
0°-40°	3123.0	71.1
0°-60°	3973.2	90.4
0°-90°	4394.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4394.7	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3036	
5°	3010	284
15°	2788	783
25°	2381	1088
35°	1583	968
45°	633	514
55°	368	336
65°	242	241
75°	132	140
85°	36	41
90°	0	



TEST NUMBER: P582708

CATALOG NUMBER: HCC6W50D010BZ-HM64560827-61NDW

CANDELA DISTRIBUTION (FULL):

0°	
0°	3036.4
2.5°	3020.2
5°	3010.5
7.5°	2974.9
10°	2910.3
12.5°	2852.2
15°	2787.6
17.5°	2706.9
20°	2610.0
22.5°	2500.2
25°	2380.7
27.5°	2241.8
30°	2067.3
32.5°	1857.4
35°	1582.8
37.5°	1279.1
40°	998.2
42.5°	775.2
45°	633.1
47.5°	539.5
50°	471.6
52.5°	416.7
55°	368.2
57.5°	332.7
60°	303.6
62.5°	274.6
65°	242.2
67.5°	213.2
70°	184.1
72.5°	158.3
75°	132.4
77.5°	106.6
80°	80.8
82.5°	58.1
85°	35.5
87.5°	16.2
90°	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)