

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P582709

Luminaire Tested: **HCC6W50D010MB-HM64560827-61PSMDW**

Issue Date: 9/16/2021

Test Information

Test Method: LM-41-14
Report Number: P582709
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2105-241-12)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/16/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC6W50D010MB-HM64560827-61PSMDW
Description: HALO COMMERCIAL 6" ROUND, NEW CONSTRUCTION FRAME, WITH 6" PLASTIC TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 2700K CCT
CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4572.3 lumens
Efficiency: N/A
Efficacy: 95.3 lumens/watt
Spacing Criteria (0/90/45): 1.09 / 1.09 / 1.04
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 48
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P582709
CATALOG NUMBER: HCC6W50D010MB-HM64560827-61PSMDW

Luminous Intensity Polar Plot





TEST NUMBER: P582709
 CATALOG NUMBER: HCC6W50D010MB-HM64560827-61PSMDW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				
1	111	107	104	101	108	105	102	99	101	98	96	97	95	93	93	92	90	88				
2	103	96	91	86	101	95	90	85	91	87	83	88	85	82	85	82	80	78				
3	96	87	81	75	94	86	80	75	83	78	73	80	76	72	78	74	71	69				
4	89	80	72	67	87	78	72	66	76	70	65	74	69	65	72	67	64	62				
5	84	73	65	60	82	72	65	59	70	64	59	68	63	58	66	62	58	56				
6	78	67	59	54	77	66	59	54	64	58	53	63	57	53	61	56	53	51				
7	73	62	54	49	72	61	54	49	60	53	49	58	53	48	57	52	48	46				
8	69	57	50	45	68	57	50	45	56	49	45	54	49	44	53	48	44	43				
9	65	53	46	41	64	53	46	41	52	46	41	51	45	41	50	45	41	39				
10	62	50	43	38	60	49	43	38	49	42	38	48	42	38	47	42	38	36				

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	163424
5°	162981
10°	160551
15°	158009
20°	152806
25°	145545
30°	132888
35°	106990
40°	72114
45°	52579
50°	45448
55°	41050
60°	38944
65°	36878
70°	34685
75°	32852
80°	30559
85°	28430



TEST NUMBER: P582709
 CATALOG NUMBER: HCC6W50D010MB-HM64560827-61PSMDW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	280.3	6.1
10°-20°	781.8	17.1
20°-30°	1098.5	24.0
30°-40°	977.8	21.4
40°-50°	546.4	12.0
50°-60°	389.3	8.5
60°-70°	283.3	6.2
70°-80°	164.0	3.6
80°-90°	51.0	1.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2160.6	47.3
0°-40°	3138.4	68.6
0°-60°	4074.1	89.1
0°-90°	4572.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4572.3	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2981	
5°	2962	280
15°	2784	782
25°	2406	1098
35°	1599	978
45°	678	546
55°	430	389
65°	284	283
75°	155	164
85°	45	51
90°	0	



TEST NUMBER: P582709
CATALOG NUMBER: HCC6W50D010MB-HM64560827-61PSMDW

CANDELA DISTRIBUTION (FULL):

	0°
0°	2981.1
2.5°	2968.2
5°	2961.7
7.5°	2935.8
10°	2884.2
12.5°	2835.8
15°	2784.1
17.5°	2713.0
20°	2619.3
22.5°	2516.0
25°	2406.2
27.5°	2270.6
30°	2099.3
32.5°	1879.8
35°	1598.7
37.5°	1282.2
40°	1007.7
42.5°	804.3
45°	678.2
47.5°	594.3
50°	532.9
52.5°	478.1
55°	429.5
57.5°	390.8
60°	355.2
62.5°	323.0
65°	284.3
67.5°	251.9
70°	216.4
72.5°	184.1
75°	155.1
77.5°	126.0
80°	96.8
82.5°	71.1
85°	45.2
87.5°	22.6
90°	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)