

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P582758

Luminaire Tested: **HCC6W50D010MW-HM64560840-61MDH**

Issue Date: 9/16/2021

Test Information

Test Method: LM-41-14
Report Number: P582758
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2105-241-5)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/16/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC6W50D010MW-HM64560840-61MDH
Description: HALO COMMERCIAL 6" ROUND, NEW CONSTRUCTION FRAME, WITH 6" MEDIUM DISTRIBUTION, HAZE TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 4000K CCT CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5376.6 lumens
Efficiency: N/A
Efficacy: 112.0 lumens/watt
Spacing Criteria (0/90/45): 1.01 / 1.01 / 0.97
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 48
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P582758
CATALOG NUMBER: HCC6W50D010MW-HM64560840-61MDH

Luminous Intensity Polar Plot





TEST NUMBER: P582758
 CATALOG NUMBER: HCC6W50D010MW-HM64560840-61MDH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	113	110	108	105	111	108	106	104	104	102	100	100	99	97	97	96	94	93			93
2	107	102	98	94	105	100	96	93	97	94	91	94	91	89	91	89	87	85			85
3	101	94	89	85	99	93	88	84	90	86	83	88	84	81	86	83	80	79			79
4	96	88	82	77	94	86	81	77	84	79	76	82	78	75	80	77	74	72			72
5	90	81	75	71	89	80	75	70	79	74	70	77	73	69	75	72	68	67			67
6	85	76	70	65	84	75	69	65	74	68	64	72	67	64	71	67	63	62			62
7	81	71	65	60	79	70	64	60	69	64	60	68	63	59	67	62	59	57			57
8	77	67	60	56	75	66	60	56	65	59	55	64	59	55	63	58	55	53			53
9	73	62	56	52	72	62	56	52	61	56	52	60	55	52	59	55	51	50			50
10	69	59	53	49	68	58	52	48	57	52	48	57	52	48	56	51	48	47			47

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	269282
5°	269056
10°	266250
15°	260898
20°	247145
25°	223186
30°	189592
35°	139983
40°	80959
45°	42966
50°	24281
55°	12702
60°	8322
65°	5915
70°	4264
75°	3219
80°	2399
85°	2390



TEST NUMBER: P582758
 CATALOG NUMBER: HCC6W50D010MW-HM64560840-61MDH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	463.3	8.6
10°-20°	1285.8	23.9
20°-30°	1678.2	31.2
30°-40°	1282.4	23.9
40°-50°	464.3	8.6
50°-60°	134.9	2.5
60°-70°	48.2	0.9
70°-80°	16.5	0.3
80°-90°	3.1	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3427.3	63.7
0°-40°	4709.7	87.6
0°-60°	5308.9	98.7
0°-90°	5376.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5376.6	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	4912	
5°	4889	463
15°	4597	1286
25°	3690	1678
35°	2092	1282
45°	554	464
55°	133	135
65°	46	48
75°	15	16
85°	4	3
90°	0	



TEST NUMBER: P582758
CATALOG NUMBER: HCC6W50D010MW-HM64560840-61MDH

CANDELA DISTRIBUTION (FULL):

	0°
0°	4912.1
2.5°	4889.3
5°	4889.3
7.5°	4855.2
10°	4783.0
12.5°	4699.6
15°	4597.0
17.5°	4445.2
20°	4236.4
22.5°	3978.3
25°	3689.8
27.5°	3363.3
30°	2995.1
32.5°	2581.3
35°	2091.7
37.5°	1579.1
40°	1131.3
42.5°	781.9
45°	554.2
47.5°	398.6
50°	284.7
52.5°	201.2
55°	132.9
57.5°	95.0
60°	75.9
62.5°	60.7
65°	45.6
67.5°	37.9
70°	26.6
72.5°	19.0
75°	15.2
77.5°	11.3
80°	7.6
82.5°	3.8
85°	3.8
87.5°	0.0
90°	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)