

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P593351

Luminaire Tested: **HCC6W50D010BZ-HM64560850-61PSMDW**

Issue Date: 9/16/2021

Test Information

Test Method: LM-41-14
Report Number: P593351
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2105-241-12)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/16/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC6W50D010BZ-HM64560850-61PSMDW
Description: HALO COMMERCIAL 6" ROUND, NEW CONSTRUCTION FRAME, WITH 6" PLASTIC TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 5000K CCT
CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5372.8 lumens
Efficiency: N/A
Efficacy: 111.9 lumens/watt
Spacing Criteria (0/90/45): 1.09 / 1.09 / 1.04
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 48
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P593351
CATALOG NUMBER: HCC6W50D010BZ-HM64560850-61PSMDW

Luminous Intensity Polar Plot





TEST NUMBER: P593351
 CATALOG NUMBER: HCC6W50D010BZ-HM64560850-61PSMDW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	111	107	104	101	108	105	102	99	101	98	96	97	95	93	93	92	90	88			
2	103	96	91	86	101	95	90	85	91	87	83	88	85	82	85	82	80	78			
3	96	87	81	75	94	86	80	75	83	78	73	80	76	72	78	74	71	69			
4	89	80	72	67	87	78	72	66	76	70	65	74	69	65	72	67	64	62			
5	84	73	65	60	82	72	65	59	70	64	59	68	63	58	66	62	58	56			
6	78	67	59	54	77	66	59	54	64	58	53	63	57	53	61	56	53	51			
7	73	62	54	49	72	61	54	49	60	53	49	58	53	48	57	52	48	46			
8	69	57	50	45	68	57	50	45	56	49	45	54	49	44	53	48	44	43			
9	65	53	46	41	64	53	46	41	52	46	41	51	45	41	50	45	41	39			
10	62	50	43	38	60	49	43	38	49	42	38	48	42	38	47	42	38	36			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	192041
5°	191519
10°	188663
15°	185671
20°	179560
25°	171022
30°	156163
35°	125722
40°	84737
45°	61797
50°	53405
55°	48247
60°	45775
65°	43325
70°	40760
75°	38592
80°	35926
85°	33399



TEST NUMBER: P593351
 CATALOG NUMBER: HCC6W50D010BZ-HM64560850-61PSMDW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	329.4	6.1
10°-20°	918.7	17.1
20°-30°	1290.8	24.0
30°-40°	1149.0	21.4
40°-50°	642.1	12.0
50°-60°	457.5	8.5
60°-70°	332.9	6.2
70°-80°	192.7	3.6
80°-90°	59.9	1.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2538.9	47.3
0°-40°	3687.8	68.6
0°-60°	4787.4	89.1
0°-90°	5372.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5372.8	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3503	
5°	3480	329
15°	3272	919
25°	2827	1291
35°	1879	1149
45°	797	642
55°	505	457
65°	334	333
75°	182	193
85°	53	60
90°	0	



TEST NUMBER: P593351
CATALOG NUMBER: HCC6W50D010BZ-HM64560850-61PSMDW

CANDELA DISTRIBUTION (FULL):

	0°
0°	3503.1
2.5°	3487.8
5°	3480.3
7.5°	3449.9
10°	3389.2
12.5°	3332.3
15°	3271.5
17.5°	3188.0
20°	3077.9
22.5°	2956.5
25°	2827.4
27.5°	2668.1
30°	2467.0
32.5°	2208.8
35°	1878.6
37.5°	1506.7
40°	1184.1
42.5°	945.0
45°	797.1
47.5°	698.3
50°	626.2
52.5°	561.7
55°	504.8
57.5°	459.2
60°	417.5
62.5°	379.6
65°	334.0
67.5°	296.1
70°	254.3
72.5°	216.4
75°	182.2
77.5°	148.0
80°	113.8
82.5°	83.5
85°	53.1
87.5°	26.6
90°	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)