

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P582793

Luminaire Tested: **HCC6W50D010SL-HM64560930-61MDC**

Issue Date: 9/16/2021

Test Information

Test Method: LM-41-14
Report Number: P582793
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2105-241-4)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/16/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC6W50D010SL-HM64560930-61MDC
Description: HALO COMMERCIAL 6" ROUND, NEW CONSTRUCTION FRAME, WITH 6" MEDIUM DISTRIBUTION, SPECULAR TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT
CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5058.6 lumens
Efficiency: N/A
Efficacy: 105.4 lumens/watt
Spacing Criteria (0/90/45): 1.06 / 1.06 / 0.96
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 48
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P582793
CATALOG NUMBER: HCC6W50D010SL-HM64560930-61MDC

Luminous Intensity Polar Plot





TEST NUMBER: P582793
 CATALOG NUMBER: HCC6W50D010SL-HM64560930-61MDC

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	114	111	108	106	111	109	106	104	105	103	101		101	99	98		97	96	95	94
2	108	103	99	96	106	101	98	95	98	95	93		95	93	91		92	90	89	87
3	102	96	91	87	100	95	90	86	92	88	85		90	86	84		87	85	82	81
4	97	90	84	80	95	89	83	79	86	82	79		84	81	78		83	79	77	75
5	92	84	78	74	91	83	78	73	81	76	73		80	75	72		78	74	72	70
6	88	79	73	68	86	78	72	68	76	71	68		75	71	67		74	70	67	65
7	83	74	68	64	82	73	68	63	72	67	63		71	66	63		70	66	62	61
8	79	70	63	59	78	69	63	59	68	63	59		67	62	59		66	62	58	57
9	75	66	60	56	74	65	59	55	64	59	55		63	58	55		62	58	55	54
10	72	62	56	52	71	61	56	52	61	55	52		60	55	52		59	55	52	50

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	240222
5°	243957
10°	257855
15°	287107
20°	297742
25°	244290
30°	171185
35°	116781
40°	60835
45°	21390
50°	9578
55°	3068
60°	1765
65°	1245
70°	1026
75°	678
80°	0
85°	0



TEST NUMBER: P582793
 CATALOG NUMBER: HCC6W50D010SL-HM64560930-61MDC

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	429.4	8.5
10°-20°	1422.7	28.1
20°-30°	1811.5	35.8
30°-40°	1079.6	21.3
40°-50°	261.8	5.2
50°-60°	40.2	0.8
60°-70°	9.9	0.2
70°-80°	3.4	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3663.7	72.4
0°-40°	4743.3	93.8
0°-60°	5045.3	99.7
0°-90°	5058.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5058.6	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	4382	
5°	4433	429
15°	5059	1423
25°	4039	1812
35°	1745	1080
45°	276	262
55°	32	40
65°	10	10
75°	3	3
85°	0	0
90°	0	



TEST NUMBER: P582793
CATALOG NUMBER: HCC6W50D010SL-HM64560930-61MDC

CANDELA DISTRIBUTION (FULL):

	0°
0°	4382.0
2.5°	4382.0
5°	4433.2
7.5°	4513.5
10°	4632.2
12.5°	4818.2
15°	5058.8
17.5°	5209.6
20°	5103.7
22.5°	4696.4
25°	4038.7
27.5°	3313.8
30°	2704.3
32.5°	2210.2
35°	1745.0
37.5°	1286.3
40°	850.1
42.5°	458.7
45°	275.9
47.5°	173.3
50°	112.3
52.5°	67.3
55°	32.1
57.5°	19.3
60°	16.1
62.5°	12.9
65°	9.6
67.5°	6.4
70°	6.4
72.5°	3.2
75°	3.2
77.5°	3.2
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)