

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P582805

Luminaire Tested: **HCC6S50D010MB-HM64560930-61WDW**

Issue Date: 9/16/2021

Test Information

Test Method: LM-41-14
Report Number: P582805
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2105-241-9)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/16/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC6S50D010MB-HM64560930-61WDW
Description: HALO COMMERCIAL 6" ROUND, NEW CONSTRUCTION FRAME, WITH 6" WIDE DISTRIBUTION, WHITE TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4683.3 lumens
Efficiency: N/A
Efficacy: 97.6 lumens/watt
Spacing Criteria (0/90/45): 1.11 / 1.11 / 1.09
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 48
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P582805
CATALOG NUMBER: HCC6S50D010MB-HM64560930-61WDW

Luminous Intensity Polar Plot





TEST NUMBER: P582805
 CATALOG NUMBER: HCC6S50D010MB-HM64560930-61WDW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				
1	111	107	104	101	108	105	102	99	101	98	96	97	95	93	94	92	90	89				
2	103	97	91	87	101	95	90	86	91	87	84	88	85	82	85	83	80	78				
3	96	87	81	76	94	86	80	75	83	78	74	81	76	72	78	74	71	69				
4	89	80	72	67	87	78	72	66	76	70	66	74	69	65	72	67	64	62				
5	84	73	65	60	82	72	65	59	70	64	59	68	63	58	66	61	58	56				
6	78	67	59	54	76	66	59	54	64	58	53	63	57	53	61	56	52	51				
7	73	62	54	49	72	61	54	49	60	53	48	58	52	48	57	52	48	46				
8	69	57	50	45	68	57	50	45	55	49	44	54	48	44	53	48	44	42				
9	65	53	46	41	64	53	46	41	52	45	41	51	45	41	50	44	41	39				
10	61	50	43	38	60	49	42	38	48	42	38	47	42	38	47	41	38	36				

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	159817
5°	159718
10°	158175
15°	156533
20°	152112
25°	145684
30°	135211
35°	116332
40°	84923
45°	58184
50°	46779
55°	40773
60°	37629
65°	35776
70°	33403
75°	31242
80°	28350
85°	24216



TEST NUMBER: P582805
 CATALOG NUMBER: HCC6S50D010MB-HM64560930-61WDW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	275.1	5.9
10°-20°	774.6	16.5
20°-30°	1101.7	23.5
30°-40°	1060.6	22.6
40°-50°	610.3	13.0
50°-60°	386.7	8.3
60°-70°	273.7	5.8
70°-80°	156.0	3.3
80°-90°	44.5	1.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2151.4	45.9
0°-40°	3212.1	68.6
0°-60°	4209.0	89.9
0°-90°	4683.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4683.3	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2915	
5°	2902	275
15°	2758	775
25°	2408	1102
35°	1738	1061
45°	750	610
55°	427	387
65°	276	274
75°	148	156
85°	38	45
90°	0	



TEST NUMBER: P582805
CATALOG NUMBER: HCC6S50D010MB-HM64560930-61WDW

CANDELA DISTRIBUTION (FULL):

	0°
0°	2915.3
2.5°	2902.4
5°	2902.4
7.5°	2883.2
10°	2841.5
12.5°	2799.8
15°	2758.1
17.5°	2694.0
20°	2607.4
22.5°	2511.2
25°	2408.5
27.5°	2283.5
30°	2136.0
32.5°	1956.3
35°	1738.3
37.5°	1472.1
40°	1186.7
42.5°	936.5
45°	750.5
47.5°	631.8
50°	548.5
52.5°	481.0
55°	426.6
57.5°	378.4
60°	343.2
62.5°	311.1
65°	275.8
67.5°	243.8
70°	208.4
72.5°	176.4
75°	147.5
77.5°	118.7
80°	89.8
82.5°	64.1
85°	38.5
87.5°	16.1
90°	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)