

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P582812

Luminaire Tested: **HCC6W50D010SL-HM64560935-61MDH**

Issue Date: 9/16/2021

Test Information

Test Method: LM-41-14
Report Number: P582812
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2105-241-5)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/16/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC6W50D010SL-HM64560935-61MDH
Description: HALO COMMERCIAL 6" ROUND, NEW CONSTRUCTION FRAME, WITH 6" MEDIUM DISTRIBUTION, HAZE TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT
CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4598.8 lumens
Efficiency: N/A
Efficacy: 95.8 lumens/watt
Spacing Criteria (0/90/45): 1.01 / 1.01 / 0.97
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 48
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P582812
CATALOG NUMBER: HCC6W50D010SL-HM64560935-61MDH

Luminous Intensity Polar Plot





TEST NUMBER: P582812
 CATALOG NUMBER: HCC6W50D010SL-HM64560935-61MDH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10		0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	113	110	108	105	111	108	106	104	104	102	100	100	99	97	97	96	94	93		
2	107	102	98	94	105	100	96	93	97	94	91	94	91	89	91	89	87	85		
3	101	94	89	85	99	93	88	84	90	86	83	88	84	81	86	83	80	79		
4	96	88	82	77	94	86	81	77	84	79	76	82	78	75	80	77	74	72		
5	90	81	75	71	89	80	75	70	79	74	70	77	73	69	75	72	68	67		
6	85	76	70	65	84	75	69	65	74	68	64	72	67	64	71	67	63	62		
7	81	71	65	60	79	70	64	60	69	64	60	68	63	59	67	62	59	57		
8	77	67	60	56	75	66	60	56	65	59	55	64	59	55	63	58	55	53		
9	73	62	56	52	72	62	56	52	61	56	52	60	55	52	59	55	51	50		
10	69	59	53	49	68	58	52	48	57	52	48	57	52	48	56	51	48	47		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	230321
5°	230128
10°	227729
15°	223151
20°	211389
25°	190898
30°	162164
35°	119725
40°	69244
45°	36756
50°	20767
55°	10857
60°	7127
65°	5059
70°	3638
75°	2754
80°	2052
85°	2013



TEST NUMBER: P582812
 CATALOG NUMBER: HCC6W50D010SL-HM64560935-61MDH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	396.3	8.6
10°-20°	1099.7	23.9
20°-30°	1435.4	31.2
30°-40°	1096.9	23.9
40°-50°	397.2	8.6
50°-60°	115.3	2.5
60°-70°	41.3	0.9
70°-80°	14.1	0.3
80°-90°	2.6	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2931.4	63.7
0°-40°	4028.3	87.6
0°-60°	4540.8	98.7
0°-90°	4598.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4598.8	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	4201	
5°	4182	396
15°	3932	1100
25°	3156	1435
35°	1789	1097
45°	474	397
55°	114	115
65°	39	41
75°	13	14
85°	3	3
90°	0	



TEST NUMBER: P582812
CATALOG NUMBER: HCC6W50D010SL-HM64560935-61MDH

CANDELA DISTRIBUTION (FULL):

	0°
0°	4201.4
2.5°	4181.9
5°	4181.9
7.5°	4152.8
10°	4091.0
12.5°	4019.7
15°	3931.9
17.5°	3802.1
20°	3623.5
22.5°	3402.7
25°	3156.0
27.5°	2876.7
30°	2561.8
32.5°	2207.9
35°	1789.0
37.5°	1350.7
40°	967.6
42.5°	668.8
45°	474.1
47.5°	341.0
50°	243.5
52.5°	172.1
55°	113.6
57.5°	81.1
60°	65.0
62.5°	52.0
65°	39.0
67.5°	32.5
70°	22.7
72.5°	16.2
75°	13.0
77.5°	9.7
80°	6.5
82.5°	3.2
85°	3.2
87.5°	0.0
90°	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)