

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P582833

Luminaire Tested: **HCC6W50D010BZ-HM64560940-61NDH**

Issue Date: 9/16/2021

Test Information

Test Method: LM-41-14
Report Number: P582833
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2105-241-2)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/16/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC6W50D010BZ-HM64560940-61NDH
Description: HALO COMMERCIAL 6" ROUND, NEW CONSTRUCTION FRAME, WITH 6" NARROW DISTRIBUTION, HAZE TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 4000K CCT CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4861.0 lumens
Efficiency: N/A
Efficacy: 101.3 lumens/watt
Spacing Criteria (0/90/45): 0.89 / 0.89 / 0.89
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 48
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P582833
CATALOG NUMBER: HCC6W50D010BZ-HM64560940-61NDH

Luminous Intensity Polar Plot





TEST NUMBER: P582833
 CATALOG NUMBER: HCC6W50D010BZ-HM64560940-61NDH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10		0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	113	111	108	106	111	109	106	104	105	103	101	101	99	98	97	96	95	93		
2	108	103	99	96	106	101	98	94	98	95	92	95	93	90	92	90	89	87		
3	102	96	91	87	100	95	90	86	92	88	85	90	86	84	87	85	82	81		
4	97	90	84	80	95	88	83	79	86	82	78	84	81	78	82	79	77	75		
5	92	84	78	74	91	83	77	73	81	76	73	79	75	72	78	74	71	70		
6	88	79	73	68	86	78	72	68	76	71	68	75	71	67	74	70	67	65		
7	83	74	68	64	82	73	67	63	72	67	63	71	66	63	70	66	62	61		
8	79	70	64	59	78	69	63	59	68	63	59	67	62	59	66	62	59	57		
9	75	66	60	56	74	65	59	56	64	59	55	63	59	55	62	58	55	54		
10	72	62	56	52	71	62	56	52	61	56	52	60	55	52	59	55	52	51		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	297569
5°	296307
10°	289301
15°	274621
20°	244782
25°	206189
30°	164272
35°	117202
40°	63025
45°	27003
50°	12281
55°	4483
60°	2204
65°	1725
70°	1603
75°	699
80°	1042
85°	0



TEST NUMBER: P582833
 CATALOG NUMBER: HCC6W50D010BZ-HM64560940-61NDH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	508.3	10.5
10°-20°	1341.3	27.6
20°-30°	1553.5	32.0
30°-40°	1074.1	22.1
40°-50°	310.2	6.4
50°-60°	53.4	1.1
60°-70°	13.6	0.3
70°-80°	5.2	0.1
80°-90°	1.3	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3403.0	70.0
0°-40°	4477.2	92.1
0°-60°	4840.8	99.6
0°-90°	4861.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4861.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	5428	
5°	5384	508
15°	4839	1341
25°	3409	1553
35°	1751	1074
45°	348	310
55°	47	53
65°	13	14
75°	3	5
85°	0	1
90°	0	



TEST NUMBER: P582833
CATALOG NUMBER: HCC6W50D010BZ-HM64560940-61NDH

CANDELA DISTRIBUTION (FULL):

0°	
0°	5428.1
2.5°	5404.6
5°	5384.5
7.5°	5324.3
10°	5197.1
12.5°	5043.0
15°	4838.8
17.5°	4550.7
20°	4195.9
22.5°	3804.0
25°	3408.8
27.5°	3003.8
30°	2595.1
32.5°	2186.6
35°	1751.3
37.5°	1299.2
40°	880.7
42.5°	555.9
45°	348.3
47.5°	224.4
50°	144.0
52.5°	87.0
55°	46.9
57.5°	26.8
60°	20.1
62.5°	16.8
65°	13.3
67.5°	10.0
70°	10.0
72.5°	6.7
75°	3.3
77.5°	3.3
80°	3.3
82.5°	3.3
85°	0.0
87.5°	0.0
90°	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)