

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P593367

Luminaire Tested: **HCC6W50D010MW-HM64560950-61MDW**

Issue Date: 9/16/2021

Test Information

Test Method: LM-41-14
Report Number: P593367
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2105-241-6)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/16/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC6W50D010MW-HM64560950-61MDW
Description: HALO COMMERCIAL 6" ROUND, NEW CONSTRUCTION FRAME, WITH 6" MEDIUM DISTRIBUTION, WHITE TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 5000K CCT CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4623.4 lumens
Efficiency: N/A
Efficacy: 96.3 lumens/watt
Spacing Criteria (0/90/45): 1.08 / 1.08 / 1.03
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 48
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P593367
CATALOG NUMBER: HCC6W50D010MW-HM64560950-61MDW

Luminous Intensity Polar Plot





TEST NUMBER: P593367
 CATALOG NUMBER: HCC6W50D010MW-HM64560950-61MDW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20		
RC	80				70				50				30				10		0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10		0
RCR																			
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102		100
1	111	108	104	101	109	105	102	100	101	99	96	97	95	94	94	92	91		89
2	104	97	92	87	101	95	90	86	92	88	84	89	85	82	86	83	81		79
3	97	88	82	76	94	87	81	76	84	79	75	81	77	73	79	75	72		70
4	90	80	73	68	88	79	73	67	77	71	67	75	70	66	73	68	65		63
5	84	74	66	61	82	73	66	61	71	65	60	69	64	59	67	63	59		57
6	79	68	61	55	77	67	60	55	65	59	55	64	58	54	62	58	54		52
7	74	63	55	50	73	62	55	50	61	54	50	59	54	50	58	53	49		48
8	70	58	51	46	69	58	51	46	57	50	46	55	50	46	54	49	45		44
9	66	54	47	43	65	54	47	42	53	47	42	52	46	42	51	46	42		40
10	62	51	44	39	61	50	44	39	49	43	39	49	43	39	48	43	39		37

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	172113
5°	171478
10°	168612
15°	165642
20°	159917
25°	151636
30°	137926
35°	110209
40°	73538
45°	52416
50°	43674
55°	38077
60°	35962
65°	33869
70°	31127
75°	29060
80°	26424
85°	23147



TEST NUMBER: P593367
 CATALOG NUMBER: HCC6W50D010MW-HM64560950-61MDW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	294.7	6.4
10°-20°	819.5	17.7
20°-30°	1145.2	24.8
30°-40°	1008.8	21.8
40°-50°	545.0	11.8
50°-60°	364.4	7.9
60°-70°	258.3	5.6
70°-80°	145.2	3.1
80°-90°	42.3	0.9
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2259.4	48.9
0°-40°	3268.2	70.7
0°-60°	4177.6	90.4
0°-90°	4623.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4623.4	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3140	
5°	3116	295
15°	2919	819
25°	2507	1145
35°	1647	1009
45°	676	545
55°	398	364
65°	261	258
75°	137	145
85°	37	42
90°	0	



TEST NUMBER: P593367
CATALOG NUMBER: HCC6W50D010MW-HM64560950-61MDW

CANDELA DISTRIBUTION (FULL):

	0°
0°	3139.6
2.5°	3122.8
5°	3116.1
7.5°	3086.0
10°	3029.0
12.5°	2975.5
15°	2918.6
17.5°	2841.6
20°	2741.2
22.5°	2630.8
25°	2506.9
27.5°	2363.1
30°	2178.9
32.5°	1951.4
35°	1646.8
37.5°	1315.4
40°	1027.6
42.5°	809.9
45°	676.1
47.5°	585.8
50°	512.1
52.5°	451.9
55°	398.4
57.5°	361.5
60°	328.0
62.5°	294.5
65°	261.1
67.5°	227.6
70°	194.2
72.5°	164.0
75°	137.2
77.5°	110.4
80°	83.7
82.5°	60.2
85°	36.8
87.5°	16.8
90°	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)