

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P592982

Luminaire Tested: **HCC6S05D010MB-HM60525850-61MDH**

Issue Date: 9/16/2021

Test Information

Test Method: LM-41-14
Report Number: P592982
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2105-241-5)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/16/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC6S05D010MB-HM60525850-61MDH
Description: HALO COMMERCIAL 6" ROUND, NEW CONSTRUCTION FRAME, WITH 6" MEDIUM DISTRIBUTION, HAZE TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 5000K CCT CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 709.4 lumens
Efficiency: N/A
Efficacy: 118.2 lumens/watt
Spacing Criteria (0/90/45): 1.01 / 1.01 / 0.97
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 6
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P592982
CATALOG NUMBER: HCC6S05D010MB-HM60525850-61MDH

Luminous Intensity Polar Plot





TEST NUMBER: P592982

CATALOG NUMBER: HCC6S05D010MB-HM60525850-61MDH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	113	110	108	105	111	108	106	104	104	102	100	100	99	97	97	96	94	93	93	93	93
2	107	102	98	94	105	100	96	93	97	94	91	94	91	89	91	89	87	85	85	85	85
3	101	94	89	85	99	93	88	84	90	86	83	88	84	81	86	83	80	79	79	79	79
4	96	88	82	77	94	86	81	77	84	79	76	82	78	75	80	77	74	72	72	72	72
5	90	81	75	71	89	80	75	70	79	74	70	77	73	69	75	72	68	67	67	67	67
6	85	76	70	65	84	75	69	65	74	68	64	72	67	64	71	67	63	62	62	62	62
7	81	71	65	60	79	70	64	60	69	64	60	68	63	59	67	62	59	57	57	57	57
8	77	67	60	56	75	66	60	56	65	59	55	64	59	55	63	58	55	53	53	53	53
9	73	62	56	52	72	62	56	52	61	56	52	60	55	52	59	55	51	50	50	50	50
10	69	59	53	49	68	58	52	48	57	52	48	57	52	48	56	51	48	47	47	47	47

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	35534
5°	35500
10°	35131
15°	34427
20°	32611
25°	29451
30°	25017
35°	18464
40°	10684
45°	5667
50°	3198
55°	1673
60°	1107
65°	778
70°	561
75°	424
80°	316
85°	314



TEST NUMBER: P592982
 CATALOG NUMBER: HCC6S05D010MB-HM60525850-61MDH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	61.1	8.6
10°-20°	169.7	23.9
20°-30°	221.4	31.2
30°-40°	169.2	23.9
40°-50°	61.2	8.6
50°-60°	17.8	2.5
60°-70°	6.4	0.9
70°-80°	2.2	0.3
80°-90°	0.4	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	452.2	63.7
0°-40°	621.5	87.6
0°-60°	700.5	98.7
0°-90°	709.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	709.4	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	648	
5°	645	61
15°	607	170
25°	487	221
35°	276	169
45°	73	61
55°	18	18
65°	6	6
75°	2	2
85°	0	0
90°	0	



TEST NUMBER: P592982
CATALOG NUMBER: HCC6S05D010MB-HM60525850-61MDH

CANDELA DISTRIBUTION (FULL):

	0°
0°	648.2
2.5°	645.1
5°	645.1
7.5°	640.6
10°	631.1
12.5°	620.1
15°	606.6
17.5°	586.6
20°	559.0
22.5°	525.0
25°	486.9
27.5°	443.8
30°	395.2
32.5°	340.6
35°	275.9
37.5°	208.4
40°	149.3
42.5°	103.2
45°	73.1
47.5°	52.5
50°	37.5
52.5°	26.6
55°	17.5
57.5°	12.5
60°	10.1
62.5°	8.0
65°	6.0
67.5°	5.0
70°	3.5
72.5°	2.5
75°	2.0
77.5°	1.5
80°	1.0
82.5°	0.5
85°	0.5
87.5°	0.0
90°	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)