

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P582949

Luminaire Tested: **HCC6W05D010BZ-HM60525930-61WDW**

Issue Date: 9/16/2021

**Test Information**

Test Method: LM-41-14  
Report Number: P582949  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2105-241-9)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 9/16/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: HALO COMMERCIAL  
Catalog Number: HCC6W05D010BZ-HM60525930-61WDW  
Description: HALO COMMERCIAL 6" ROUND, NEW CONSTRUCTION FRAME, WITH 6" WIDE DISTRIBUTION, WHITE TRIM  
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT CYLINDER  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 597.4 lumens  
Efficiency: N/A  
Efficacy: 99.6 lumens/watt  
Spacing Criteria (0/90/45): 1.11 / 1.11 / 1.09  
Luminous Opening: Circular (Dia: 0.5' x H: 0')  
CIE Type: Direct

Input Watts (W): 6  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P582949  
CATALOG NUMBER: HCC6W05D010BZ-HM60525930-61WDW

### Luminous Intensity Polar Plot





TEST NUMBER: P582949  
 CATALOG NUMBER: HCC6W05D010BZ-HM60525930-61WDW

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20		
RC	80				70				50				30				10		0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10		0
RCR																			
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102		100
1	111	107	104	101	108	105	102	99	101	98	96	97	95	93	94	92	90		89
2	103	97	91	87	101	95	90	86	91	87	84	88	85	82	85	83	80		78
3	96	87	81	76	94	86	80	75	83	78	74	81	76	72	78	74	71		69
4	89	80	72	67	87	78	72	66	76	70	66	74	69	65	72	67	64		62
5	84	73	65	60	82	72	65	59	70	64	59	68	63	58	66	62	58		56
6	78	67	59	54	76	66	59	54	64	58	53	63	57	53	61	56	52		51
7	73	62	54	49	72	61	54	49	60	53	48	58	52	48	57	52	48		46
8	69	57	50	45	68	57	50	45	55	49	44	54	48	44	53	48	44		42
9	65	53	46	41	64	53	46	41	52	45	41	51	45	41	50	44	41		39
10	61	50	43	38	60	49	42	38	48	42	38	47	42	38	47	41	38		36

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	20388
5°	20377
10°	20179
15°	19972
20°	19409
25°	18582
30°	17256
35°	14844
40°	10835
45°	7419
50°	5961
55°	5209
60°	4791
65°	4553
70°	4264
75°	4003
80°	3599
85°	3082



TEST NUMBER: P582949  
 CATALOG NUMBER: HCC6W05D010BZ-HM60525930-61WDW

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	35.1	5.9
10°-20°	98.8	16.5
20°-30°	140.6	23.5
30°-40°	135.3	22.7
40°-50°	77.8	13.0
50°-60°	49.3	8.3
60°-70°	34.9	5.8
70°-80°	19.9	3.3
80°-90°	5.6	0.9
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	274.5	45.9
0°-40°	409.8	68.6
0°-60°	537.0	89.9
0°-90°	597.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	597.4	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	372	
5°	370	35
15°	352	99
25°	307	141
35°	222	135
45°	96	78
55°	54	49
65°	35	35
75°	19	20
85°	5	6
90°	0	



TEST NUMBER: P582949  
CATALOG NUMBER: HCC6W05D010BZ-HM60525930-61WDW

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	371.9
2.5°	370.3
5°	370.3
7.5°	367.8
10°	362.5
12.5°	357.2
15°	351.9
17.5°	343.7
20°	332.7
22.5°	320.4
25°	307.2
27.5°	291.3
30°	272.6
32.5°	249.6
35°	221.8
37.5°	187.8
40°	151.4
42.5°	119.4
45°	95.7
47.5°	80.6
50°	69.9
52.5°	61.4
55°	54.5
57.5°	48.3
60°	43.7
62.5°	39.7
65°	35.1
67.5°	31.1
70°	26.6
72.5°	22.5
75°	18.9
77.5°	15.1
80°	11.4
82.5°	8.1
85°	4.9
87.5°	2.0
90°	0.0

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)