

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P582958

Luminaire Tested: **HCC6S05D010MB-HM60525935-61NDC**

Issue Date: 9/16/2021

**Test Information**

Test Method: LM-41-14  
Report Number: P582958  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2105-241-1)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 9/16/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: HALO COMMERCIAL  
Catalog Number: HCC6S05D010MB-HM60525935-61NDC  
Description: HALO COMMERCIAL 6" ROUND, NEW CONSTRUCTION FRAME, WITH 6" NARROW DISTRIBUTION, SPECULAR TRIM  
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT  
CYLINDER  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 656.2 lumens  
Efficiency: N/A  
Efficacy: 109.4 lumens/watt  
Spacing Criteria (0/90/45): 0.93 / 0.93 / 0.88  
Luminous Opening: Circular (Dia: 0.5' x H: 0')  
CIE Type: Direct

Input Watts (W): 6  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P582958  
CATALOG NUMBER: HCC6S05D010MB-HM60525935-61NDC

### Luminous Intensity Polar Plot





TEST NUMBER: P582958  
 CATALOG NUMBER: HCC6S05D010MB-HM60525935-61NDC

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20			
RC	80				70				50				30				10		0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	114	111	108	106	111	109	107	105	105	103	101	101	100	98	98	97	96	94		
2	108	103	99	96	106	102	98	95	98	96	93	96	93	91	93	91	89	87		
3	103	97	92	88	101	95	91	87	93	89	86	90	87	84	88	85	83	82		
4	98	90	85	81	96	89	84	80	87	83	79	85	81	79	83	80	78	76		
5	93	85	79	75	91	84	78	75	82	77	74	80	76	73	79	75	73	71		
6	88	80	74	70	87	79	73	69	77	73	69	76	72	68	75	71	68	67		
7	84	75	69	65	83	74	69	65	73	68	64	72	67	64	71	67	64	62		
8	80	71	65	61	79	70	65	61	69	64	60	68	63	60	67	63	60	59		
9	76	67	61	57	75	66	61	57	65	60	57	65	60	57	64	60	56	55		
10	73	63	58	54	72	63	57	54	62	57	54	61	57	53	61	56	53	52		

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	39185
5°	39264
10°	39912
15°	40199
20°	36747
25°	28877
30°	21136
35°	14997
40°	7092
45°	2706
50°	1211
55°	335
60°	132
65°	117
70°	80
75°	106
80°	0
85°	0



TEST NUMBER: P582958  
 CATALOG NUMBER: HCC6S05D010MB-HM60525935-61NDC

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	68.3	10.4
10°-20°	195.8	29.8
20°-30°	217.8	33.2
30°-40°	136.0	20.7
40°-50°	32.3	4.9
50°-60°	4.6	0.7
60°-70°	1.0	0.1
70°-80°	0.5	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	481.8	73.4
0°-40°	617.8	94.2
0°-60°	654.7	99.8
0°-90°	656.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	656.2	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	715	
5°	714	68
15°	708	196
25°	477	218
35°	224	136
45°	35	32
55°	4	5
65°	1	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P582958  
CATALOG NUMBER: HCC6S05D010MB-HM60525935-61NDC

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	714.8
2.5°	711.8
5°	713.5
7.5°	716.1
10°	717.0
12.5°	716.5
15°	708.3
17.5°	680.7
20°	629.9
22.5°	558.3
25°	477.4
27.5°	399.8
30°	333.9
32.5°	279.2
35°	224.1
37.5°	164.6
40°	99.1
42.5°	57.3
45°	34.9
47.5°	22.4
50°	14.2
52.5°	8.1
55°	3.5
57.5°	1.7
60°	1.2
62.5°	1.2
65°	0.9
67.5°	0.9
70°	0.5
72.5°	0.5
75°	0.5
77.5°	0.5
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)